



Nitrile

Offers tactility and comfortable protection across numerous applications

- Made of a soft nitrile formulation for comfortable fit and feel
- Lightweight construction for tactile sensitivity and fine motor control
- Designed for a broad range of applications across all industries
- Textured on the fingertips for secure handling of tools and materials



Industries

- Food Processing
- Janitorial / Sanitation
- Healthcare
- Automotive
- Manufacturing
- Life Sciences

Recommended For

- Food processing and handling
- Standard patient examinations
- Laboratory analysis
- Catering/Meal preparation
- Light assembly tasks
- Light duty maintenance
- Multipurpose use: Dish Washing, Cleaning, Pet Care & Grooming, Food Preparation, Gardening & many more!



TECHNICAL DATA SHEET

PRODUCT INFORMATION

	92-134
Material	Nitrile
Color	Blue
Glove Design	Chlorinated, Powder-Free, Textured Fingers
Cuff	Beaded
Manufacturing/QMS Audit Standards	ISO 9001
Regulatory/Standards Compliance	ASTM D6319, FDA21 CFR 177-2600, ISO 13485, ISO 9001, US QSR/FDA 510(k) Medical Examination Grade
Packaging	100 gloves per dispenser, 10 dispensers per case, 1000 gloves per case
Storage	Keep out of direct sunlight; store in a cool and dry place. Keep away from sources of ozone or ignition.
Country of Origin	Malaysia
User Needs Segment	High Touch
Available sizes	S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
Anti-static	No

PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D6319
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151
Palm Thickness (mm/mils)	0.07 / 2.8		ASTM D6319
Finger Thickness (mm/mils)	0.09 / 3.5		ASTM D6319
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	14	14	ASTM D412 & D573
Elongation at Break (%)	500	400	ASTM D412 & D573
Force at break (N)	6	6	EN 455-2

ORDERING INFORMATION

Size	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
Product Code	92134070	92134080	92134090	92134100

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

Russia

Ansell PYC
Ten. +7 495 258 13 16

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.