

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-561

All-day comfort & cut protection



Cut



Light Duty

The thinnest, lightest ISO C/ANSI A3-level industrial gloves, with 200% greater durability

- **Optimized durability:** Hyflex® 11-561 industrial safety gloves are 200% more durable than competitors, with FORTIX™ Abrasion Resistance Technology
- **Advanced protection:** The safety gloves' patented INTERCEPT™ Cut Resistance Technology guards against lacerations
- **Thoughtful features:** The 11-561's palm coating improves grip, while their reinforced thumb crotch defends against rapid wear
- **Elevated comfort:** HyFlex® 11-561 industrial working gloves are also light and thin, making them flexible, yet protective
- **Reduced irritation:** Silicone-, fiberglass- and DMF-free, these HyFlex gloves boast Oeko-Tex™ certification for skin-friendliness
- **Proven excellence:** HyFlex® 11-561 PPE gloves satisfy EN and ANSI norms for cut and abrasion resistance

Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Mining
- Oil and gas
- Automotive Aftermarket

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges
- Assembly & inspection of components
- Applying finish to materials, products



HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-561

All-day comfort & cut protection

Key Features

- **FORTIX™ Technology:** For 200% more durability than competitive gloves
- **INTERCEPT™ yarn:** Greater hand protection, fewer workplace injuries
- **Palm coating:** For breathable PPE gloves with superior grip

Technologies



DMF free



Fibre glass free



FORTIX™
Abrasion Resistance Technology



INTERCEPT™
Cut Resistance Technology

Performance Standards & Regulatory Compliance

REACH Compliant



4X42C



CUT



ABR



dermatest-guarantee.de



Tested for harmful substances.
www.oeko-tex.com/standard100

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex [®] 11-561	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Nylon, HPPE, Basalt, Spandex, Polyester Cuff Style: Knitwrist	15	5, 6, 7, 8, 9, 10, 11, 12	210-285 mm	Grey	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.