

**RUNS LONGER,
SHINES BRIGHTER
& THIS CLASS I, DIV 1 FLASHLIGHT
IS NOW HANDSFREE!**

- Class I, Div 1 ATEX/IECEx Zone 0
- One light, 2 modes – High and Low
- Runs 24 hours on Low and 7 hours on High
- Two magnets: one on integrated belt clip and one at base of flashlight
- Drop rating of 2 meters
- Tail cap slot for lanyard



ACCESSORIES:

Helmet Clip
Item#10B-226















CLIP AND BASE MAGNETS FOR HANDSFREE LIGHTING.

HIGH MODE

LOW MODE

SPECIFICATIONS

SAFETY RATINGS

FL1 STANDARDS		FL1 STANDARDS	
 325 LUMENS	 7 h	 125 LUMENS	 24 h
 14,000 cd	 2m	 7,000 cd	 2m
 236m	 1m	 167m	 1m

POWER SOURCE: 3 AA-cell Alkaline Batteries

LAMP: Advanced LED Technology

COLOR: High-Vis Yellow

LIGHT OUTPUT: High 325 Lumens, Low 125 Lumens

PEAK BEAM INTENSITY: High 14,000 Candela, Low 7,000 Candela

BEAM DISTANCE: High 236 meters, Low 167 meters

INGRESS PROTECTION: Waterproof 1 Meter IPX7

RUN TIME: High 7 Hours, Low 24 Hours

WEIGHT: 8 oz.

LENGTH: 7.125 in. **WIDTH:** 2 in. **HEIGHT:** 2 in.

SAFETY RATINGS

UL 913
Class I Div 1 & 2 A-D
Class II Div 1 & 2 E-G
Class III Div 1 & 2
T2

ATEX/IECEx/UKCA

II 1G Ex ia op is IIC T2 Ga

ACCESSORIES

#23863 - 6 1/2" Orange
Slip Over Wand

See it all.™

