



Features

- Measures indoor/outdoor temperature and humidity
- User selectable unit of measure °F/°C
- Internal memory stores min/max temperature and humidity readings
- Waterproof sensor for outdoor temperature measurement with 6' (72") cable
- Built-in alarm clock and time display
- Desktop or wall mount
- Includes battery

Specifications

Temperature (IN)

Range: -10 to 50°C (14 to 122°F)
 Accuracy: -10 to 0°C (14 to 32°F): ±2°C (3.6°F)
 0 to 40°C (32 to 104°F): ±1°C (1.8°F)
 40 to 50°C (104 to 122°F): ±2°C (3.6°F)
 Resolution: 0.1°C (0.1°F)

Temperature (OUT)

Range: -40 to 50°C (-40 to 122°F)
 Accuracy: -40 to 0°C (-40 to 32°F): ±2°C (3.6°F)
 0 to 40°C (32 to 104°F): ±1°C (1.8°F)
 40 to 50°C (104 to 122°F): ±2°C (3.6°F)
 Resolution: 0.1°C (0.1°F)

Humidity

Range: 20 to 95% RH
 Accuracy*: 40 to 80% RH: ±5% RH
 <40 and >80% RH: ±8% RH
 Resolution: 1% RH

General Specifications

Humidity Comfort Icons: Wet/Comfort/Dry
 Sampling Time: 10 seconds
 Temperature Probe Length: 6' (72")
 Alarm Clock/Time Display: Yes
 Max/Min Functions: Yes (IN/OUT/RH)
 Product Certifications: CE, RoHS
 Power Supply: 1 "AAA" Battery
 Operating Temperature: -10 to 50°C (14 to 122°F)
 Dimensions: 5.1 x 1 x 3.1"
 (130 x 22 x 78 mm)
 Weight: 3.9 oz (110 g)

*Based on indoor temperature conditions between 64.4 and 82.4°F (18 to 28°C)

Model	Description
R6000	Temperature & Humidity Monitor