

Twist-Lock® Devices
 30A, 125/250V AC, 3 Pole, 4 Wire Grounding
 Insulgrip® Connector

HUBBELL

Features

- Superior cord grip design protects terminations from excess strain.
- Clear, funnel shaped wire entry for ease of termination.
- Integral dust shield protects wiring chamber from dust or contaminants.

Ordering Information

| Description | Cord Diameter | UPC | Catalog Number |
|------------------------|---------------------|--------------|----------------|
| Black and white nylon. | .350"-1.150" (9-29) | 783585039176 | HBL2713 |

Listings

Listed to UL 498
 Fed.Spec. W-C-596
 Certified to CSA C22.2 No.42

Specifications


| | |
|----------------------|---|
| Housing / Cord Clamp | Nylon |
| Terminal Retainer | Clear polycarbonate |
| Contacts | Brass |
| Terminal Screws | #10-32 Brass (Phillips / Slotted / Robertson) |
| Terminal Clamp | Cold rolled steel – nickel plated |
| Assembly Screws | Steel - nickel plated |

Performance

| | |
|-------------------------|--|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Terminal Accommodation | #16 AWG - #8 AWG stranded copper wire only. |
| Terminal Identification | Terminals identified in accordance with UL 498 |
| Environmental | |
| Flammability | HB or better per UL94 or CSA 22.2 No. 0.6 |
| Operating Temperatures | Maximum Continuous 75°C Minimum -40°C (w/o impact) |



30A 125/250V AC
 NEMA L14-30R
 UL/CSA
 2(2)HP



Accessories

| | |
|-------------------|---------|
| Plug | HBL2711 |
| Weatherproof Boot | HBL6036 |
| Flanged Inlet | HBL2715 |
| Weatherproof Boot | HBL6035 |

Resources

Customer Use Drawing
 eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

