



Main

| | |
|------------------------------------|----------------------|
| Range | TeSys |
| Product or Component Type | Terminal block |
| Device short name | LA7K |
| Accessory / separate part category | Connection accessory |
| Mounting support | Rail |
| Product Compatibility | LR2K LR7K |

Complementary

| | |
|-------------------------|--|
| Connections - terminals | Screw clamp terminals 1 0.00...0.01 in ² (1.5...4 mm ²)solid Screw clamp terminals 2 0.00...0.01 in ² (1.5...4 mm ²)solid Screw clamp terminals 1 0.00...0.01 in ² (0.75...4 mm ²)flexible without cable end Screw clamp terminals 2 0.00...0.01 in ² (0.75...4 mm ²)flexible without cable end Screw clamp terminals 1 0.00...0.00 in ² (0.34...2.5 mm ²)flexible with cable end Screw clamp terminals 2 0.00...0.00 in ² (0.34...1.5 mm ²)flexible with cable end |
| Tightening torque | 7.08 Lbf.in (0.8 N.m) screw clamp terminals Philips No 2 7.08 lbf.in (0.8 N.m) screw clamp terminals flat Ø 6 mm |
| Height | 3.15 in (80 mm) |
| Width | 1.77 in (45 mm) |
| Depth | 2.95 in (75 mm) |
| Net Weight | 0.22 lb(US) (0.1 kg) |
| Quantity per Set | Set of 10 |

Ordering and shipping details

| | |
|-----------------------|---------------------------------|
| Category | 22341 - CONTACTOR,D,K,&F ACCESS |
| Discount Schedule | I12 |
| GTIN | 3389110447880 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1.76 oz (50 g) |
| Returnability | Yes |
| Country of origin | CZ |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.89 in (4.8 cm) |
| Package 1 width | 2.36 in (6 cm) |
| Package 1 Length | 2.95 in (7.5 cm) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 50 |
| Package 2 Weight | 6.43 lb(US) (2.916 kg) |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|