

# CP 150



## 8-DAY PAINTER'S MATE GREEN® BRAND PAINTER'S TAPE — MULTI-SURFACE



### TYPICAL APPLICATIONS

- For interior use on painted walls, woodwork, glass, metal and vinyl

### PRODUCT FEATURES

- Medium adhesion
- Conforms well to curved or uneven surfaces
- UV-resistant
- Delivers crisp paint lines
- Removes cleanly for up to 8 days, even in direct sunlight

### CONSTRUCTION

Overall Grade/Function: 8-Day

Backing: Crepe paper

Adhesive: Rubber-based

### STANDARD WIDTH(S)

6mm 18 mm 24 mm 36 mm 48 mm 72 mm

### STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



### PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	14 lbs/in width	24.5 N/10 mm
Adhesion to Stainless Steel	29 oz/in width	3.17 N/10 mm
Thickness	5.4 mils	0.14 mm
Elongation	12%	12%
Adhesion to Backing	8 oz/in width	0.8 N/10 mm
Maximum Service Temperature	150 F	66 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

### APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

