

# CP 27<sup>®</sup>

**Shurtape<sup>®</sup>**  
TRUE TO YOUR WORK<sup>™</sup>

## 14-DAY ShurRELEASE<sup>®</sup> PAINTER'S TAPE — MULTI-SURFACE

### TYPICAL APPLICATIONS

- For interior and exterior use on multiple surfaces, including painted walls, glass, vinyl, metal and wood
- Not recommended for use on wallpaper, unpainted wallboard, ceiling tile or with uncured coatings

### PRODUCT FEATURES

- Medium adhesion
- UV-resistant
- Easy, no-residue removal
- Prevents lifting and paint seepage for cleaner paint lines
- Removes cleanly up to 14 days without surface damage

### CONSTRUCTION

Overall Grade/Function: Premium  
Backing: Crepe paper  
Adhesive: Synthetic rubber-based

### STANDARD WIDTH(S)

18 mm 24 mm 36 mm 48 mm

### STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



### PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	24 lbs/in width	42.0 N/10 mm
Adhesion to Stainless Steel	32 oz/in width	3.5 N/10 mm
Thickness	5.3 mils	0.13 mm
Elongation	8%	8%
Service Temperature Range	50 F to 200 F	10 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

