

DAYMARK ADHESIVES

DM DissolveMark®

DISSOLVE-A-WAY™ LABELS

Description	Working Temp Range	Minimum Application Temp
<ul style="list-style-type: none"> Dissolves in any water temperature leaving no sticky residue Dissolves in 30 seconds eliminating labor costs due to scrubbing adhesive Available in Day-of-the-Week, shelf life and blank labels to meet your needs 100% Biodegradable FSC Chain of Custody Certified 	-40° to 176°F -40° to 80°C	21°F -6°C
For Use in These Areas:	  	




MM MoveMark™

REMOVABLE LABELS

Description	Working Temp Range	Minimum Application Temp
<ul style="list-style-type: none"> Removes easily from containers at room temperature reducing labor and time used removing adhesive residue from containers Detach-Tab technology allows for 3 levels of adhesion to fit your application 	-40° to 160°F -40° to 71°C	10°F -12°C
For Use in These Areas:	    	

CM CoolMark™

FREEZABLE LABELS

Description	Working Temp Range	Minimum Application Temp
<ul style="list-style-type: none"> Can be applied as low as 0°F and the strong adhesive stays on any surface Moisture resistant so imprint remains legible through thawing process Adheres to frozen containers and can also be applied at room temperature 	-40° to 160°F -40° to 71°C	0°F -18°C
For Use in These Areas:	  	

THE DIFFERENCE IS NIGHT AND DAY.™

800.847.0101

daymark.com



#2267
092721



DAYMARK ADHESIVES



PERMANENT LABELS

Description	Working Temp Range	Minimum Application Temp
<ul style="list-style-type: none"> Aggressive adhesive stays on any surface, working in multiple applications Variety of templates available including Day-Of-The-Week and deli labels Adhesive marking identified on every label with DK 	-40° to 160°F -40° to 71°C	10°F -12°C
For Use in These Areas: <div style="display: flex; justify-content: space-around; margin-top: 10px;">   </div>		



REPOSITIONABLE LABELS

Description	Working Temp Range	Minimum Application Temp
<ul style="list-style-type: none"> Adhesive can be repositioned and can adhere to another container or lid Transferable making them perfect for HACCP records and HACCP books Easy to remove leaving no adhesive residue on reusable containers 	-20° to 250°F -29° to 121°C	25°F -4°C
For Use in These Areas: <div style="display: flex; justify-content: space-around; margin-top: 10px;">     </div>		



TEAR-PROOF REPOSITIONABLE LABELS

Description	Working Temp Range	Minimum Application Temp
<ul style="list-style-type: none"> Synthetic label coating can be used almost any environment, including steam Repositionable adhesive is easy to remove and can be transferred and reused multiple times 	-20° to 250°F -29° to 121°C	25°F -4°C
For Use in These Areas: <div style="display: flex; justify-content: space-around; margin-top: 10px;">     </div>		

THE DIFFERENCE IS NIGHT AND DAY.™

800.847.0101

daymark.com

