# XVBC35

Harmony XVB, Illuminated unit for modular tower lights, plastic, orange, Ø70, steady, bulb or LED not included, 250 V





#### Main

Range of Product	Harmony XVB Universal
Product or Component Type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit
Signalling type	Steady
Mounting diameter	2.76 in (70 mm)
Component name	XVBC
Material	Polycarbonate
Light source	Bulb not included, orange
Bulb type	Incandescent BA 15d Protected LED
[Us] rated supply voltage	<= 250 V

## Complementary

Assembly style	Customer assembly, up to 5 units	
Maximum power dissipation in W	7 W	
Connections - terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end	
[Ui] rated insulation voltage	250 V IEC 60947-1	
Nominal voltage limit	0.851.1 Un IEC 60947-5-1	
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1	
CAD overall width	2.76 in (70 mm)	
CAD overall height	2.48 in (63 mm)	
CAD overall depth	2.76 in (70 mm)	

### **Environment**

Pollution degree	2
Product Certifications	CSA C22-2 No 14 UL 508 CCC GOST
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)
Ambient air temperature for operation	-13122 °F (-2550 °C) LED -13158 °F (-2570 °C) incandescent
Electrical shock protection class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
IP degree of protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
NEMA degree of protection	NEMA 4X UL 508 indoor)

# Ordering and shipping details

Category	22611 - XVB-STACKLIGHTS	
Discount Schedule	XV	
GTIN	3389110845082	
Nbr. of units in pkg.	1	
Package weight(Lbs)	4.76 oz (135 g)	
Returnability	Yes	
Country of origin	ID	

# Packing Units

<b>3</b>	
Unit Type of Package 1	PCE
Package 1 Height	3.23 in (8.2 cm)
Package 1 width	3.74 in (9.5 cm)
Package 1 Length	3.23 in (8.2 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Weight	11.87 lb(US) (5.382 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	288
Package 3 Weight	117.03 lb(US) (53.084 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

# Offer Sustainability

Sustainable offer status	s Green Premium product	
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
REACh Regulation	REACh Declaration	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EVEN RoHS  Declaration	
Mercury free	Yes	
RoHS exemption information	€Yes	
China RoHS Regulation	☐ China RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	

## Contractual warranty


Warranty	18 months

# XVBC35

## Indicator Bank without "Flash" Discharge Tube Unit

#### **Dimensions**

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.




- (1) Base unit XVBC21, to be ordered separately
- (2) Illuminated or audible signalling unit
- (3) Cover (supplied with XVBC21 base unit)

Number of illuminated or audible signalling units (no "flash")	b in mm	b in in.
1	138	5.43
2	201	7.91
3	264	10.39
4	327	12.87
5	390	15.35

## Indicator Bank with "Flash" Discharge Tube Unit

#### **Dimensions**

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit
- (3) "Flash" unit, to be ordered separately

Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06