XVBC4B4

Harmony XVB, Illuminated unit for modular tower lights, plastic, red, Ø70, flashing, for bulb or LED, 24 V AC, 24...48 V DC





Main

Range of Product	Harmony XVB Universal
Product or Component Type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit
Signalling type	Flashing
Mounting diameter	2.76 in (70 mm)
Component name	XVBC
Material	Polycarbonate
Light source	Bulb not included, red
Bulb type	Incandescent BA 15d Protected LED Incandescent
[Us] rated supply voltage	24 V AC 2448 V DC

Complementary

Customer assembly, up to 5 units	
7 W	
Screw clamp terminals, <= 1 x 1.5 mm² with cable end	
250 V IEC 60947-1	
0.851.1 Un IEC 60947-5-1	
4 kV IEC 60947-1	
1 Hz	
2.76 in (70 mm)	
2.48 in (63 mm)	
2.76 in (70 mm)	
0.35 lb(US) (0.16 kg)	
	7 W Screw clamp terminals, <= 1 x 1.5 mm² with cable end 250 V IEC 60947-1 0.851.1 Un IEC 60947-5-1 4 kV IEC 60947-1 1 Hz 2.76 in (70 mm) 2.48 in (63 mm) 2.76 in (70 mm)

Environment

Pollution degree	2	
Product Certifications	UL 508 CSA C22-2 No 14 GOST CCC	
Standards	EN/IEC 60947-5-1	
Protective treatment	TC	
Ambient Air Temperature for Storage	-40158 °F (-4070 °C)	
Ambient air temperature for operation	-13122 °F (-2550 °C) incandescent -13122 °F (-2550 °C) LED	
Electrical shock protection class	Class I on support tube IEC 61140 Class II on base unit IEC 61140	
IP degree of protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529	
NEMA degree of protection	NEMA 4X UL 508 indoor)	

Ordering and shipping details

Category	22611 - XVB-STACKLIGHTS	
Discount Schedule	XV	
GTIN	3389110845136	
Nbr. of units in pkg.	1	
Package weight(Lbs)	5.15 oz (146 g)	
Returnability	Yes	
Country of origin	ID	

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.15 in (8 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	3.66 in (9.3 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Weight	12.77 lb(US) (5.794 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

Offer Sustainability

ustainable offer status Green Premium product		
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
REACh Regulation	REACh Declaration	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
Mercury free	Yes	
RoHS exemption information	₫Yes	
China RoHS Regulation	☑ China RoHS Declaration	
Environmental Disclosure	☐ Product Environmental Profile	
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	

Contractual warranty


- Contraction from the contract of	
Warranty	18 months

Product data sheet Dimensions Drawings

Indicator Bank without "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.




- (1) Base unit XVBC21, to be ordered separately
- (2) Illuminated or audible signalling unit
- (3) Cover (supplied with XVBC21 base unit)

Number of illuminated or audible signalling units (no "flash")	b in mm	b in in.
1	138	5.43
2	201	7.91
3	264	10.39
4	327	12.87
5	390	15.35

Indicator Bank with "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit
- (3) "Flash" unit, to be ordered separately

Number of illuminated or audible signalling units other than "flash" tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06