



## Main

Range	9080LB
Product	Power Distribution Block
Current Rating	760 A copper

## Complementary

Voltage Rating	600 V AC/DC
Mounting Type	Surface mount
Number of poles	3
Terminals per Pole	2 line 8 load
Wire Size	Line 8, AWG 4...500 kcmil, copper Load 2, AWG 14...AWG 2/0, copper
Electrical Connection	Tin plated copper lugs
SCCR	100 kA UL 508 A
Ambient air temperature for operation	-40...302 °F (-40...150 °C)
Block Material	Phenolic block
Terminal Tightening Torque	Load lug 40 lbf.in (4.52 N.m) AWG 8 copper Load lug 35 lbf.in (3.95 N.m) AWG 14...AWG 10 copper Line lug 375 lbf.in (42.37 N.m) AWG 4...500 kcmil copper Load lug 120 lbf.in (13.56 N.m) AWG 6...AWG 1 copper
Wire stripping length	Load 0.75 in (19.05 mm) top Line 1.13 in (28.70 mm) Load 1.38 in (35.05 mm) bottom
Height	5.5 in (139.70 mm)
Width	8.54 in (216.92 mm)
Depth	3.13 in (79.50 mm)
End Barrier	9080LB53

## Environment

Certifications	CSA file 70361 class 6228 01 UL recognized E60616 CCN XCFR2 CE
----------------	--

## Ordering and shipping details

Category	21711 - 9080 LB
Discount Schedule	CP1
GTIN	785901097693
Nbr. of units in pkg.	1
Package weight(Lbs)	5.36 lb(US) (2.431 kg)
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.80 in (9.652 cm)
Package 1 width	5.80 in (14.732 cm)
Package 1 Length	8.80 in (22.352 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Weight	32.92 lb(US) (14.932 kg)
Package 2 Height	12.50 in (31.75 cm)
Package 2 width	9.60 in (24.384 cm)
Package 2 Length	13.00 in (33.02 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------