

GEORGIAN™ GEORGIAN™ HIGH WASHABILITY

Square Lay-in & Tegular
medium texture



CAD/Revit® drawings at:
armstrongceilings.com/cadrevit



▲ Georgian™ Beveled Tegular panels with Prelude® XL® 15/16" suspension system

Medium-texture panels with a unique splatter-painted visual and options for high washability. Offer standard or Total Acoustics® panel performance.

KEY SELECTION ATTRIBUTES

- Get total noise control and floor plan versatility with Total Acoustics® ceiling panels: NRC + CAC = Total Acoustics Performance (items 795 and 796 only)
- Unique splatter-painted visual
- Mold- and mildew-resistant surface
- High Washability items available
 - Meets USDA/FSIS guidelines for use in food processing establishments
- Durable – Washable
Scrubbable
Impact-resistant
Scratch-resistant
- 30-Year Limited System Warranty against visible sag (excludes item 791 and other sizes), mold, and mildew

TYPICAL APPLICATIONS

- Schools/classrooms (Items 795, 796)
- Corridors/conference rooms
- Kitchen/food preparation areas (Items 793, 794)

COLOR



White
(WH)

DETAILS (Other Suspension Systems compatible. Refer to listing on next page.)



1. Georgian™ Beveled Tegular
2. Georgian™ Beveled Tegular with Prelude® 15/16" suspension system
3. Georgian™ Beveled Tegular with Silhouette® 9/16" suspension system 1/4" Reveal

GEORGIAN™ GEORGIAN™ HIGH WASHABILITY

Square Lay-in & Tegular
medium texture

GREENGUARD
Gold Certified
(details below)

LEED™ WELL™ LBC UP TO **56% RECYCLED CONTENT**

energy management construction waste mgmt regional materials design for flexibility EPD recyclable/excise producer resp. biobased materials recycled content sourcing of raw materials material ingredient reporting low emitting materials lighting quality acoustics

Calculate sustainability with GreenGenie™
armstrongceilings.com/greengenie

LOCATION DEPENDENT

VISUAL SELECTION

armstrongceilings.com/catdwgs	Susp. Dwg.	Item No.	Dimensions (Inches)
GEORGIAN™ 15/16" Square Lay-in	1	764	24 x 24 x 5/8" □
		763	24 x 48 x 5/8" □
		791	30 x 60 x 3/4" □
15/16" Beveled Tegular	15	1752	24 x 24 x 5/8" □
9/16" Beveled Tegular	29, 44, 48, 52, 56	1753	24 x 24 x 5/8" □
GEORGIAN™ High Washability Panels, Unperforated 15/16" Square Lay-in	1	794	24 x 24 x 5/8" □
		793	24 x 48 x 5/8" □
SCHOOL ZONE® GEORGIAN 15/16" Square Lay-in	1	796	24 x 24 x 3/4" □
		795	24 x 48 x 3/4" □
Made-to-Order Sizes SCHOOL ZONE® GEORGIAN			3/4" Thick – 15/16" Square Lay-in
		Width	Length
		12" - 30"	18" - 72"

3-4 WEEKS
order to ship


PERFORMANCE SELECTION

Dots represent high level of performance.

UL Classified Acoustics		Total Acoustics ¹	Fire Performance	Light Reflect	Anti-Mold/Mildew	Sag Resist	Certified Low VOC Emissions	DURABILITY				Recycle Program	30-Yr Warranty
NRC +	CAC	NRC CAC	Class	Light Reflect	Anti-Mold/Mildew	Sag Resist	Certified Low VOC Emissions	Wash	Scrub	Impact	Scratch	Recycle Program	30-Yr Warranty
0.55	33	N/A	Class A	0.86	•	•	•	N/A	N/A	•	•	•	•
0.55	33	N/A	Class A	0.86	•	•	•	N/A	N/A	•	•	•	•
0.55	33	N/A	Class A	0.86	•	Std	•	N/A	N/A	•	•	•	1-Yr
0.55	35	N/A	Class A	0.86	•	•	•	N/A	N/A	•	•	•	•
0.55	35	N/A	Class A	0.86	•	•	•	N/A	N/A	•	•	•	•
N/A	33	N/A	Class A	0.88	•	•	•	•	•	•	•	•	•
N/A	33	N/A	Class A	0.88	•	•	•	•	•	•	•	•	•
0.65	35	GOOD	Class A	0.86	•	•	•	N/A	N/A	•	•	•	•
0.65	35	GOOD	Class A	0.86	•	•	•	N/A	N/A	•	•	•	•
N/A	N/A	N/A	Class A	0.86	•	•	•	N/A	N/A	•	•	•	1-Yr

¹ Total Acoustics® ceiling panels have an ideal combination of sound absorption and sound blocking in one product.
GOOD (NRC 0.60-0.65; CAC 35+) BETTER (NRC 0.70-0.75; CAC 35+) BEST (NRC 0.80+; CAC 35+)

SUSPENSION SYSTEMS



PHYSICAL DATA

Material
Wet-formed mineral fiber

Surface Finish
Factory-applied latex paint

Fire Performance
Class A: ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index of 25 or less. Smoke Developed Index of 50 or less (UL labeled).

ASTM E1264 Classification
Type III, Form 2, Pattern C E Items 794, 793, 898 – Type IX, Form 2, Pattern G Fire Class A

Sag Resistance
HumiGuard® Plus ceiling panels are recommended for areas subject to high humidity, up to, but not including, standing water and outdoor applications. Excludes Item 791 and made-to-order panels.

Anti-Mold/Mildew
Ceiling tiles with BioBlock® performance resist the growth of mold and mildew on the tile surface.

VOC Emissions
GREENGUARD Gold Certified
Third-party certified compliant with California Department of Public Health CDPH/EHLB/Standard Method Version 1.2, 2017. This standard is the guideline for low emissions in LEED®, WELL Building Standard™, Living Building Challenge® (LBC), CalGreen Title 24, ANSI/ASHRAE/USGBC/IES Standard 189; ANSI/GBI Green Building Assessment Protocol.

High Recycled Content
Contains greater than 50% total recycled content. Total recycled content based on product composition of post-consumer and pre-consumer (post-industrial) recycled content per FTC guidelines.

PRODUCT CERTIFIED FOR LOW CHEMICAL EMISSIONS
UL.COM/GG UL 2818



Insulation Value
R Factor - 1.6 (BTU units)
R Factor - 0.28 (Watts units)

30-Year Performance Guarantee & Warranty
When installed with Armstrong® Suspension System. Details at armstrongceilings.com/warranty

Weight; Square Feet/Carton
763, 793 – 0.67 lbs/SF; 96 SF/ctn
764, 794, 1752, 1753 – 0.72 lbs/SF; 64 SF/ctn
791 – 0.76 lbs/SF; 75 SF/ctn
796 – 1 lbs/SF; 48 SF/ctn
795 – 1 lbs/SF; 64 SF/ctn

Minimum Order Quantity
1 carton, excludes made-to-order panels

Metric Items Available
1753M, 764M, 763M, 791M, 1752M, 796M, 795M, 794M, 793M – Metric items are subject to extended lead times and minimum quantities. Contact your representative for more details.