

# HONEYWELL PERFECT FIT GLOVES

Balance protection with dexterity, cut protection, comfort and grip

## CHOOSE SAFETY GLOVES THAT PROVIDE THE PERFECT FIT

The Honeywell Perfect Fit gloves are engineered to be lightweight, glass fiber-free, and coated with a specialty engineered Polyurethane (PU); this PU coating is designed with a low level of dimethylformamide (DMF) which protects your workers at a higher level.

### INDUSTRIES

- Automotive
- Machinery and Equipment
- Metal Fabrication
- Warehousing and Logistics
- Manufacturing
- Construction
- Transportation

### APPLICATIONS

- Handling sharp objects
- Painting and surface inspections
- Chassis assembly
- Mounting and dismantling
- Maintenance
- Fastening components and parts



We engineered the Honeywell Perfect Fit Gloves using advanced technologies and unique features.

The gloves are designed to help workers perform at their best with enhanced comfort, dexterity, grip and protection.

Low content level of dmf (<100)

Color coded markings

QR code with quick access to tech info

Silicon-free option

Coating breathability

Glass-fiber free for comfort

Light weight

Washable (up to 5 cycles of washing)

High grip performance

High grip performance

Glass-fiber free for comfort

Color coded markings

Silicon-free option

Washable

Coating breathability



QR Code with quick access to tech info (on the care label).

Lightweight

Low content level of dmf (<100)

**Honeywell**

# HONEYWELL PERFECT FIT GLOVES ORDERING INFORMATION

SKU	PRODUCT	QR CODE	GAUGE	COATING / LINER MATERIAL	CUT LEVEL & COLOR CODING	ANSI/ISEA 105:2016		EN 388:2016
						ABRASION	PUNCTURE	
NPF21-1118G			18	Grey polyurethane/Nylon, Palm dipped	A1 A	3	2	2X21A
NPF21-1118W			18	White polyurethane/White Nylon, Palm dipped, Silicone free	A1 A	3	2	2X21A
NPF22-7113G			13	Grey polyurethane/Dyneema, Palm dipped	A2 B	6	2	4X43B
NPF22-7113W			13	White polyurethane/Dyneema, Palm dipped, Silicone free	A2 B	6	2	4X43B
NPF23-0113G			13	Grey polyurethane/ HPPE, Basalt, Palm dipped	A3 C	6	3	4X43C
NPF23-0113W			13	White polyurethane/ HPPE, Basalt, Palm dipped, Silicone free	A3 C	6	3	4X43C
NPF24-0113G			13	Grey polyurethane/ HPPE, Basalt, Palm dipped	A4 D	6	3	4X44D
NPF25-9113G			13	Grey polyurethane/ Stainless steel, Palm dipped	A5 E	6	3	4X44E
NPF26-9113G			13	Grey polyurethane/ Stainless Steel, Palm dipped	A6 F	6	4	4X44F
NPF26-9623G			13	Grey natural rubber/Stainless Steel, 3/4 dipped	A6 F	3	4	3X44F

**Packaging:** inner pack of 10 pairs

**Available Sizes:** 6/XS, 7/S, 8/M, 9/L, 10/XL, 11/XXL

## For more information

[sps.honeywell.com](http://sps.honeywell.com)

Technical Service: 800.873.5242

## Honeywell Personal Protective Equipment (PPE)

855 S Mint St Charlotte, NC 28202

US: Canada:

Tel. 800.430.5490 Tel. 888.212.7233

Fax. 800.322.1330 Fax. 888.667.8477

Honeywell Perfect Fit Datasheet | v1 | 02/22  
© 2022 Honeywell International Inc.

