

SYCLONE® JR. RECHARGEABLE AREA LIGHT

MARKET
APPLICATIONS: Law Enforcement, Sporting Goods, Security, Fire & Rescue, Hardware/Tool, Automotive, Industrial, Consumer

DESCRIPTION:

The Syclone® Jr. has high and low outputs and uses a cool white LED for max illumination. The body can rotate 360° in its frame and is adjustable using one hand. The light will stand on its base and includes magnets that will hold it on any ferrous metal surface (in any orientation) to provide task-specific illumination. There is also a folding hook to hang the light with for added versatility. The rechargeable battery results in one of the lowest operating costs of any area light of this type and size. Battery charging is effortless – just pull open the rubber USB cover and plug in the charge cord.

CASE MATERIAL:

Tough thermoplastic construction with an elastomer button

DIMENSIONS:

Length: 2.04 in. (5.18 cm) Width: 2.25 in. (5.71 cm) Thickness: 1.14 in. (2.89 cm)

WEIGHT:

2.0 oz (57 g)

LENS:

Acrylic, gasket sealed

LIGHT SOURCE:

LED technology, impervious to shock with a 50,000-hour lifetime

LIGHT OUTPUT:

See chart. Optimized electronics provides regulated intensity.


ON/OFF:

Depress the button momentarily to turn the light on. The light will come on in high mode. Press the button again and switch to low mode. The third press of the button will turn the light off. **NOTE:** If you wait more than two (2) seconds after the last button press, the next press of the button will turn the light off.

RUN TIME:

See chart.

BATTERY:

1000 mAh Li-Polymer cell

CHARGING:

Charge time is 4.5 hours with an AC wall charger (5V/1A USB input). Charge times will vary when using just the USB/micro-USB cord, depending on the voltage the USB source provides. Charge indication is provided in the on/off button. Red is charging, green is charged.

FEATURES:


LED technology for extreme brightness
 IPX4-rated for water resistant operation
 2-meter impact resistance tested
 Micro-USB rechargeable

WARRANTY:





Streamlight warrants its Syclone® Jr. "non-replaceable 1000mAh lithium polymer battery rated at 300-400 discharges" will be free from manufacturing defects under normal use for 24 months after purchase. During the warranty period, at its sole discretion, Streamlight will repair or replace any defective part or product.

APPROVALS:
 Meets applicable European Community Directives

 CEC Compliant

OPTIONAL
ACCESSORIES:

N/A

| | FL 1 STANDARD | HIGH | LOW |
|-----------|---|-------------------|------------------|
| OUTPUT |  | 210 LUMENS | 85 LUMENS |
| RUN TIME |  | 3h 45m | 8h 30m |
| DISTANCE |  | 79m | 49m |
| INTENSITY |  | 1550cd | 600cd |

PERFORMANCE CURVE
