

The high-performance ProTac® 2.0 headlamp produces 2,000 lumens without sacrificing run time. Powered by the new SL-B50® battery pack that charges inside or outside of the light using a USB-C cord.



TEN-TAP® Programmable switch

Adjustable elastic head strap



Metal sleeve protects the USB-C port. Slide to the right to access. Charges directly via USB-C port in the body of the SL-B50® battery.



CHARGING



CHARGED

Streamlight SL-B50® protected Li-Ion USB-rechargeable battery pack with on-board safety control. Recharges in 6 hours.

TEN-TAP® Programmable switch allows user selection of one of three different programs: 1.) High/medium/low 2.) High only; 3.) Low/high
Three lighting modes: – High for super-bright light: 2,000 lumens; 241m beam; runs 2.25 hours – Medium for bright light and longer run time: 650 lumens; 130m beam; runs 4.5 hours – Low for extended run time: 110 lumens; 55m beam; runs 25 hours
6000 series machined aircraft aluminum with Type II MIL-Spec anodized finish

IP64-rated; dust-tight and water-resistant. All openings O-ring sealed.
10.48 oz. (297g)
Limited Lifetime Warranty Visit streamlight.com for full warranty information
Uses Streamlight SL-B50® protected Li-Ion rechargeable battery
#89001 - ProTac 2.0 Headlamp - SL-B50® battery pack, USB-C cord, elastic and rubber hard hat straps - box