




PROTAC® 2.0 HEADLAMP

- DESCRIPTION:** The ProTac® 2.0 Headlamp is a 2,000-lumen flashlight that uses a proprietary Streamlight SL-B50® protected Li-Ion rechargeable battery. The ProTac® 2.0 Headlamp features three different user selectable programs. The Streamlight SL-B50® charges directly via USB-C port in the body of the battery. The battery is keyed to ensure proper alignment of the charging port. Packaged with a USB-C cord, rubber and elastic head straps, and an SL-B50® battery.
- CASE MATERIAL:** 6000 series machined aircraft aluminum with Type II MIL-Spec anodized finish. Available in black.
- DIMENSIONS:** Body Width: 4.92 in (125 mm) Head Diameter: 1.46 in (37 mm) Head Depth: 2.56 in (65 mm)
- WEIGHT:** 10.48 oz (297 g) with (1) Streamlight SL-B50® protected Li-Ion USB-rechargeable battery (included in purchase)
- LENS:** Glass with anti-reflective coating; gasket-sealed
- LIGHT SOURCE:** LED technology, impervious to shock with a 50,000-hour lifetime
- LIGHT OUTPUT:** See chart. Fully regulated output for consistent lumen performance over the entire battery life.
- ON/OFF:** Multi-function, push-button switch. One-handed momentary/constant on operation. TEN-TAP® programmable switch allows user selection of one of three different programs: high/medium/low (factory default), high only, or low/high.
- RUN TIME:** See chart below. All run time claims are to 10% of initial lumen output.
- BATTERY:** One (1) Streamlight SL-B50® protected Li-Ion USB-rechargeable battery with on-board safety control, 4,900mAh. Recharges in 6 hours.

FEATURES:







- LED technology for extreme brightness
- IP64-rated; dust-tight and water resistant
- All openings O-ring sealed
- 2-meter impact resistance tested
- Serialized for positive identification

APPROVALS:   Meets applicable United Kingdom and European Community Directives
 CEC Compliant

WARRANTY: Streamlight's Limited Lifetime Warranty

OPTIONAL ACCESSORIES: USB-C charge cord, elastic head strap, rubber head strap, SL-B50® battery

OUTPUT:

FL 1 Standard	HIGH	MEDIUM	LOW
	2000 LUMENS	650 LUMENS	110 LUMENS
	2h 15min	4h 30min	25h
	241m	130m	55m
	14,500cd	4,200cd	750cd