

Article-No.: 8502353

<b>weight:</b>	1,50 kg	3,31 lbs
<b>Nominal WLL:</b>	4000 kg	8800 lbs
<b>A:</b>	50 mm	1-31/32"
<b>B:</b>	82 mm	3-1/4"
<b>T:</b>	125 mm	4-15/16"
<b>C:</b>	54 mm	2-1/8"
<b>D:</b>	61 mm	2-13/32"
<b>E:</b>	64 mm	2-1/2"
<b>F:</b>	18 mm	11/16"
<b>G:</b>	43 mm	1-11/16"
<b>H:</b>	41 mm	1-5/8"
<b>I:</b>	130 mm	5-1/8"
<b>K:</b>	78 mm	3-1/16"
<b>L:</b>	84 mm	3-5/16"
<b>M:</b>	1"-8UNC	1"-8UNC
<b>N:</b>	48 mm	1-7/8"

