

# 97 52 36

## KNIPEX PreciForce® Crimping Pliers



- repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Chrome vanadium electric steel in special quality, oil-hardened

For daily crimping applications, the specialist likes crimping pliers that work precisely and reliably. In addition, they should be light, comfortable to use, robust and reasonably priced: PreciForce®.

<b>Article No.</b>	97 52 36
<b>EAN</b>	4003773051893
<b>Pliers</b>	burnished
<b>Handles</b>	with multi-component grips
<b>Applications</b>	insulated terminals and plug connectors
<b>Capacity mm<sup>2</sup></b>	0,5 - 6,0
<b>Number of crimping positions</b>	3
<b>AWG</b>	20 - 10
<b>Length mm</b>	220
<b>Net weight g</b>	487

*technical change and errors excepted*

