Remco Product Selection Guide

Vikan Brooms & Scrubs



Bristle Options



■ Soft — Bristles are longer and thinner than other types; ideal for sweeping dry, fine particles like flour and sugar



 Medium — Suitable for wet and dry applications; great for sweeping larger food particles such as peelings



■ Stiff — Bristles are shorter or thicker; perfect for scrubbing difficult dirt and for wet use with cleaning agents



■ Soft/Stiff Combo — The best of both worlds, offering stiff bristles that loosen stubborn dirt and soft bristles that sweep away fine particles



 Soft/Split — Soft bristle with split ends; split bristle fibers hold more water and cleaning agent to achieve a maximum washing effect





Denotes Ultra Safe Technology

Broom Options



Sweeping Brooms — Designed to sweep environments where hygiene and efficiency are essential. Available in a variety of bristle options to accommodate cleaning and sanitation efforts.



 Deck Scrubs — Designed to remove stubborn or sticky particles from decks and floors.



Specialty Scrub Brushes — Designed to remove stubborn or sticky particles from a variety of surfaces such as walls, floors, and even grout. Waterfed options are available.



■ Tank Brushes — Clean curved surfaces easily and efficiently with the broad angled bristle arrangement of the tank brushes.

Staple Set vs UST

UST's unique design and construction improves bristle retention and allows for significantly more effective cleaning of the product itself.







Drilled & stapled UST brushware



Specialty Scrub Brushes



- The right level of clean needs the right tool, and our specialty scrub brushes get the job done with distinct bristle patterns, stiffness, and angles.
- The Grout Brush (7040x) has an arrow shaped bristle pattern designed to deliver effective cleaning performance to the natural cracks, crevices, and grout lines of tiled surfaces.
- The angled bristles on the High-Low Brush (7047x) were designed to clean the area where the wall meets the floor, as well as in exposed drains and gulleys.
- The Waterfed Washing Brush w/Angle-Adjustment (7067x) can be used as a dusting brush or a wall/machine washing brush. It's waterfed design is excellent for rinsing after foaming.
- Tank Brushes (7037x and 7039x) have a unique 180 degree bristle pattern for uniform cleaning of curved surfaces.



7040x Vikan Grout Brush



7047xVikan High-Low Brush



7067xVikan Waterfed Washing
Brush w/Angle Adjustment



7037xVikan Tank Brush



7039x Vikan Tank Brush



Sweeping Brooms



- Angled bristles make the Angle Cut Broom (2914x) ideal for sweeping narrow spaces and collecting large particles of debris before further cleaning or sanitizing.
- Vikan Push Brooms (2915x, 2920x)
 work best over large areas, moving
 heavy debris across an area. The thick
 bristle pattern has the strength to push
 large particles and the density to keep
 from losing smaller debris.
- Often used as lobby brooms, Vikan Upright Brooms (3104x and 3166x) are ideal for sweeping narrow spaces and between production lines.
- The Fine Particle Push Broom (3178x) is suitable for dry environments. Typical uses include sweeping fine particles such has flour, starch, sugar, and other dry powders. It also performs well on dust and fine dirt.
- UST Push Brooms (3171x and 3173x)
 maximize the cleaning effort while
 minimizing potential contaminants.
 Bristle Security Units are organized
 to form a unique bristle pattern that
 provides improved efficiency and makes
 tool cleaning and inspection easier.
- The Combo Push Brooms (3174x and 3194x) are suitable for both wet and dry sweeping. The stiff front bristles loosen and push heavier debris, while the soft bristles on the back gather the finer particles. These brooms are often used in kitchens and restaurants.
- The Small Particle Push Brooms (3179x and 3199x) are suitable for sweeping particles in dry environments.
- 3194x and 3199x provide a 24" wide broom head that is useful in large areas where efficiency is important.



2914x Vikan Angle Broom



2915xVikan 13" Push Broom



2920x Vikan 20" Push Broom



3104xVikan 10" Upright Broom



Vikan 12" Upright Broom



3178xVikan 16" Fine Particle
Push Broom



3171x Vikan 16" UST Push Broom



3173x Vikan 16" UST Push Broom



3174x Vikan 16" Combo Push Broom



Vikan 16" Small Particle
Push Broom



3194x Vikan 24" Combo Push Broom



3199xVikan 24" Small Particle
Push Broom



Deck Scrubs



- Deck scrubs, made to work with water and liquid cleaning agents, are ideal for scrubbing tough and stubborn messes.
- Waterfed Deck Scrubs (7041x and 7043x) allow a steady stream of water to move through the tool for superior cleaning power during scrubbing.
- The Narrow Flared Deck Scrub (7044x)
 has a distinct bristle pattern, allowing
 it to work well in difficult-to-reach and
 constrained areas. By applying firm
 downward pressure on the scrub,
 the bristles will reach and clean into
 awkward corners and recesses.
- Stiff bristles on the 12" Deck Scrub (7060x) and 19" Deck Scrub (7062x) provide a deep clean that removes tough debris on all types of floors; epoxy, tiles, cement, etc.
- The 12" Deck Scrub (7061x) utilizes a more gentle bristle type that allows for scrubbing a range sensitive surfaces, walls and floors included.
- The unique construction and pattern of the Bristle Security Units makes the UST Deck Scrub (7064x) very effective at scrubbing stubborn debris on both textured and smooth surfaces, particularly in high risk areas where hygiene is critical.



7041xVikan Deck Scrub



7043xVikan Deck Scrub



7044xVikan Narrow Flared
Deck Scrub



7060xVikan 12" Deck Scrub



7061x Vikan 12" Deck Scrub



7062xVikan 19" Deck Scrub



Vikan 16" UST Deck Scrub



Vikan products are designed to work exclusively with Vikan handles:

- Vikan products employ a hygienic proprietary thread that is suitable for use in food contact areas.
- Vikan hygienic threads are not compatible with products that use another thread type.
- Vikan handles can be interchanged with all other Remco and Vikan products such as scrapers, brooms, scrubs, squeegees, tube brushes, and pad holders.

For more information about Vikan and Remco handles, email cs@remcoproducts.com or call (317) 876-9856

Remco Products Corporation

4735 West 106th Street Zionsville, Indiana 46077

PHONE: 317.876.9856 | FAX: 800.585.8619

www.remcoproducts.com

© 2016 Remco Products 10/16 RMC-SG104 | Vikan® is a registered trademark of Vikan A/S. | Remco is the exclusive Vikan Partner in the United States.