

# MT300™ TR400™ TR400DT™ TR550™

## PROFESSIONAL HOT MELT GLUE GUNS



- Built-in Safety Stand
- Comfortable Contour Design
- Non-Drip Nozzle
- Tough Heat Resistant Housing
- Comfortable Contour Grip and Trigger Feed For Ease of Use
- The TR400DT has a Unique Low Temperature Setting for Use on Fragile Materials
- The TR550 Features a Built-in Drip Tray/Stand
- TR550 also Includes an Interchangeable Non-Drip Nozzle as Well as a Unique Heat System Keeps the Handle Comfortably Cool

### APPLICATIONS INCLUDE:

- Crafts
- Woodwork
- Ceramics
- Glass
- Fabrics
- Balloons
- Metals
- Plastic Foam
- Hobbies



A varied range of Arrow Hot Melt Glue Guns assures reliable, professional performance and results with every job.

## MT300™

Compact, easy to use. The Arrow Mini Glue Gun with trigger feed is ideal for arts and crafts hobbyists and do-it-yourselfers. Comes complete with convenient stand and 3 sticks of all purpose glue.

## TR400™ and TR400DT™

These versatile glue guns bond almost anything permanently in 60 seconds without the need of mixing or clamping. The

ideal tool for repairs, hobbies, arts & crafts and much more. Uses all purpose and slow set glue sticks. The TR400DT is a dual a dual temp glue gun with the capability of bonding more delicate materials without damaging them.

## TR550™

Powerful, top of the line professional hot melt model with its famous lever action trigger. The unique, full size lever action combines maximum grip strength and user comfort, with no fatigue, during long gluing projects.

## Product Specification Chart

	TR550™	TR400™	TR400DT™	MT300™
<b>Unit UPC</b>	0-79055-00002-0	0-79055-00400-4	0-79055-00406-6	0-79055-00003-7
<b>Unit Dimensions</b>	2.45"L x 6.78" W x 10"H (62.23mm x 172.21mm x 254mm)	2.00"L x 6.75"W x 9.50"H (50.8mm x 171.45mm x 241.3mm)	2.00"L x 8.83"W x 11.75"H (50.8mm x 224.25mm x 298.5mm)	1.75"L x 5.00"W x 7.40"H (44.45mm x 127mm x 187.96mm)
<b>Unit Wt</b>	.80 lbs. (.363 kilos)	.56 lbs. (.254 kilos)	.78 lbs. (.354 kilos)	.35 lbs. (.159 kilos)
<b>Master Qty</b>	12	12	12	12
<b>Master Code</b>	2-00-79055-00002-4	2-00-79055-00400-8		2-00-79055-00003-1
<b>Master Dimensions</b>	20.20"L x 11.70" W x 7.50"H (513.1mm x 297.2mm x 190.5mm)	18.80"L x 9.90"W x 7.30"H (477.5mm x 251.5mm x 185.4mm)		17.5"L x 7.75"W x 5.25"H (444.5mm x 190.9mm x 133.4mm)
<b>Master Wt</b>	11 lbs. (4.99 kilos)	7.63 lbs. (3.46 kilos)	9 lbs. (.4.08 kilos)	5 lbs. (2.27 kilos)
<b>Cubic Ft</b>	1.03	1.06	.83	.41



**Arrow Fastener Co., LLC**  
271 Mayhill Street  
Saddle Brook, New Jersey 07663  
Phone: 201-843-6900  
Fax: 201-843-3911

**Arrow Fastener Canada, Inc.**  
6505 Metropolitan Blvd. East  
Montreal, Quebec H1P 1X9  
Phone: 514-321-3983  
Fax: 514-321-9424

**Arrow Fastener (U.K.) Ltd.**  
Unit 5, ZK Park 23 Commerce Way  
Croydon CRO 4ZS, Surrey  
Phone: 44.208.686.9180  
Fax: 44.208.686.9197

UPC	Item	Description	Qty/ Pak	Qty Ctn	Wt	Cu Ft
07055-000051	AP5	4" All Purpose Glue Stix	6	24	4 lb	0.15
079055-000068	SS6	4" Slow Set Glue Stix	6	24	4 lb	0.15
079055-000105	BAP5-4	4" All Purpose Glue Stix	24	24	14 lb	0.50
079055-002468	BSS6-4	4" Superpower Slow Set	24	24	14 lb	0.50
079055-000112	AP10-4	10" All Purpose Glue Stix	12	24	17 lb	0.50
20079055-011402	AP1000	Bulk 4" All Purpose 1,140 Stix Approximately	25	25	25	0.75
20079055-045605	AP2000	Bulk 10" All Purpose 450 Stix Approximately	25	25	25 lb	0.75
10079055-000065	SS1000	Bulk 4" Slow Set 1,140 Approximately	25	25	25	0.75