

Wall Mount Intercom

Designed for single-channel, two-way indoor and outdoor communication applications, Wall-Mount Intercoms feature integrated volume control, TALK/LISTEN switch, corrosion resistant cast aluminum housing with rugged powder coat finish (Type 4X, IP56 enclosure), reliable 25-watt speaker, and balanced line output. Heavy duty units are UL listed, CSA Certified and Marine rated; and available in 12 or 24VDC and 120 or 240 VAC, 50/60Hz models.

- Heavy-duty industrial intercom for indoor or outdoor application
- Single channel, two-way communications
- Integrated volume control and Talk/Listen switch
- Balanced line output
- 25 watt speaker
- Cast aluminum housing with rugged powder coat finish
- Available; 12 or 24VDC and 120 or 240VAC, 50/60Hz
- UL listed, CSA Certified, Marine Rated
- Type 4X, IP56 enclosure



Model	Voltage	Operating Current	Stand-by Current	Frequency Response
AD-26	12VDC	1.47A	100mA	320Hz to 8.0Khz
AD-27	120VAC	240mA	83 mA	320Hz to 8.0Khz
AD-56	24VDC	1.65A	100mA	320Hz to 8.0Khz
AD-57	240VAC	127mA	83mA	320Hz to 8.0Khz

Optional Features

- Call Button (A), Sends call tone to other intercoms on the same audio line.
- Master (C), controls Talk/Listen function of a Slave unit.
- Slave (D), allows hands free operation, default Talk mode
- Remote Power (-1), 120VAC unit can supply power to a 12VDC unit remotely.
- Foot Pedal Ready (-2), hands free operation of the Talk/Listen switch, pedal sold separately.
- Auxiliary Signal (-3), remote call button activated contact closure to activate local strobe for additional attention gathering. *Note: For AC units, this feature is only available in combination with a call button (A).*
- Extreme Conditions (-4), Extreme cold temperature operation -50°F to 150°F
- Zoned System Remote (-6), designed to be a remote unit in a zoned system.
- Contact factory for zone design assistance.
- Noise Cancelling Microphone Ready (-7), equipped with a jack for hand held microphone sold separately.
- Pre-Amp Equipped (-8), pre-amp to power a remote speaker. Note: For DC units, this feature is only available in combination with the remote volume control (-M44) feature.
- Remote Volume Control Equipped (-M44), equipped with volume control for remote speaker.

Note: Some restrictions apply when combining optional features. Consult factory for details.

Product Specifications

Speaker Rating	30 watt	30 watt
Operating temp	-31°F to 150°F	-50°C to 66°C
Net weight	9.0 lbs	4.08 Kg
Shipping weight	11 lbs	4.99 Kg
Dimensions:		
Height	9.90 in	25.15 cm
Width	6.70 in	17.02 cm
Depth	3.88 in	9.86 cm

