

Lab-Tips® - LT070R

Small Open Cell Foam Swab with Rigid Tip

Cleanroom laundered 100 ppi reticulated foam sock head swab

The LT070R Swab is an excellent general purpose swab for cleaning small and confined areas. It's cleanroom laundered open cell foam head combines superior cleanliness with particle entrapment capability.

A small rigid handle and rigid core provide firm support and precise control.



Key Attributes

- Cleanroom laundered polyurethane foam over rigid core
- 100 ppi open cell reticulated foam
- Thermally bonded head
- Laundered and packaged in Class 10 {ISO Class 4} cleanroom

Benefits

- Low particles, fibers, ions and extractables
- Good chemical resistance
- Soft and non-abrasive with no contaminating adhesives
- Good sorbency and excellent solvent hold
- Free from Silicone, amides and DOP

Environmental

- Complies with RoHS 2002/05 and REACH requirements

Applications

- Designed for the highest level of contamination control in critical processing applications
- Cleaning of sensitive equipment
- Applying lubricants and other liquids
- Removing excess materials

Physical Characteristics

Head Material	Open Cell Foam	Handle Thickness	2.8mm {0.110"}
Head Width	4mm {0.157"}	Handle Length	58mm {2.28"}
Head Thickness	4mm {0.157"}	Total Swab Length	70mm {2.75"}
Head Length	12.5mm {0.492"}	Head Bond	Thermal
Handle Material	Polypropylene	Handle Text	Berkshire
Handle Width	2.8mm {0.110"}		

Other Foam sock tip swabs

- LT070P Pointed swab
- LT01465 Long handle swab
- LT070F Flexible internal head

Americas	Tel 1 413 528 2602	Fax 1 413 528 2614	info@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 3 5827 2380	Fax 81 3 5827 2382	master@berkshire.co.jp

Technical Data:

ATTRIBUTE		LTO70R	TEST METHOD
Non-Volatile Residue	IPA mg/swab	0.035	IEST-RP.CC004.3, Sec 7.1.2
Ions (µg/swab)	Chloride	0.044	IEST-RP.CC004.3, Sec 7.2.2
	Sulfate	0.022	
	Nitrate	ND*	
	Phosphate	ND*	
	Fluoride	ND*	
	Potassium	0.0038	
	Calcium	0.024	
	Sodium	0.081	
	Magnesium	0.0043	

Notes:

- Data shown are typical values
- Due to differences in test methods applied and equipment utilized by different swab manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- * ND* = below the detection limit of the equipment.

Order Information:

Product	Part Number	Size	Swabs/Pk	Pks/Cs	Case size
Small Foam w/ Rigid Tip	LT070R.20	70mm	100	20	235 x 105 x 85mm