

Lab-Tips® - LTP1465

Long Handle Knitted Polyester Swab

Cleanroom laundered double layer 100% polyester knit swab

The LTP1465 long handled polyester knit swab is a general purpose swab specially suited for cleaning hard to reach areas. Its flexible paddle tip and durable cleanroom laundered knit head are excellent for rigorous cleaning applications.



Key Attributes

- Cleanroom laundered 100% continuous filament polyester knit head
- Long polypropylene handle with a flexible paddle head
- Thermally bonded head
- Laundered and packaged in Class 10 {ISO Class 4} cleanroom

Benefits

- Critically low particles, fibers, ions and extractables
- High abrasion resistance for rigorous cleaning applications
- Excellent chemical resistance
- No contaminating adhesives
- Good sorbency
- Autoclavable
- Free from Silicone, amides and DOP

Environmental

- Complies with RoHS 2002/05 and REACH requirements

Applications

- Designed for the highest level of contamination control in critical processing applications
- Cleaning of sensitive equipment
- Applying lubricants and other liquids
- Surface sampling
- Cleaning validation
- Cleaning with solvents

Physical Characteristics

Head Material	Knitted Polyester	Handle Thickness	3.1mm {0.122"}
Head Width	7mm {0.275"}	Handle Length	145mm {5.71"}
Head Thickness	4mm {0.157"}	Total Swab Length	162mm {6.38"}
Head Length	16.8mm {0.661"}	Head Bond	Thermal
Handle Material	Polypropylene	Handle Text	Berkshire
Handle Width	3.1mm {0.122"}		

Other Knitted Polyester tip swabs

- LTP70F Short handle flexible tip
- LTP70R Short handle rigid head
- LTP125 Large head

Americas	Tel 1 413 528 2602	Fax 1 413 528 2614	info@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 3 5827 2380	Fax 81 3 5827 2382	master@berkshire.co.jp

Technical Data:

ATTRIBUTE		LTP1465	TEST METHOD
Non-Volatile Residue	IPA mg/swab	0.045	IEST-RP.CC004.3, Sec 7.1.2
Ions (µg/swab)	Chloride	0.035	IEST-RP.CC004.3, Sec 7.2.2
	Sulfate	0.023	
	Nitrate	ND*	
	Phosphate	ND*	
	Fluoride	ND*	
	Potassium	0.044	
	Calcium	0.036	
	Sodium	0.015	
	Magnesium	0.0052	

Notes:

- Data shown are typical values
- Due to differences in test methods applied and equipment utilized by different swab manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- * ND* = below the detection limit of the equipment.

Order Information:

Product	Part Number	Size	Swabs/pk	Pks/cs	Case size
Long Handle Knit Polyester	LTP1465.10	162mm	100	10	180 x 150 x 170mm