

# C404830S4 WIRE CONTAINER



## PRODUCT SHEET

### C404830S4 without Casters

### C404830S4C with Casters

The side and base mesh is 2"x2" (5 x5 cm). The gate is a ½ Drop Front Gate with only four latch bolts to engage for quick and easy assembly. The **C404830S4** has four way entry for forklifts and pallet jacks, with a clearance of 4.5" (11.4 cm). Can be stacked up to four high fully loaded. Heavy-duty base design for long life cycles. The casters are 4"x2" Phenolic, 2 Rigid and 2 Swivel.

Weight (lbs/kg)	153/69 without casters 171/77.5 with casters	Capacity	4000/1814 without casters 2800/1270 with casters
Overall dimensions W x L x H (in/cm)	40 x 48 x 36½ 102 x 122 x 93	Inside dimensions W x L x H (in/cm)	38 x 46 x 30 96.5 x 117 x 76
Surface Treatment	Plating	Electro-Zinc	
Accessories	Casters, Security Lid, Vertical Divider, Bar Runners, Caster Brakes, Colors (special order)		
Shipment	Packed Folded & Stacked (with or without casters)		



**NashvilleWire**

P R O D U C T S

For more information about this product:

[nwpsales@nashvillewire.com](mailto:nwpsales@nashvillewire.com)

[www.nashvillewire.com](http://www.nashvillewire.com)

800-448-2125