

511 CADDY® EZ RISER for Copper Tube

5110200CP



Features

- Recommended for suspending vertical type K or L copper tubing risers
- Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 8)
- Slotted holes make assembly easy, eliminating loose hardware
- Bolts are accessible from the front, serrated washer head design means no wrench required on back side for tightening

Product Specifications

Part Number	5110200CP
Material	Steel
Finish	Copper electro plated
Pipe Size	2"
Outer Diameter (OD)	2 1/8"
Hole Size (HS)	7/16"
Length (L)	1 1/2"
A	10 3/8"
B	1 1/4"
Screw Diameter (Sc)	3/8"
Screw Length (L)	1 1/2"
Static Load (F)	150 lb
Standard Packaging Quantity	25 pc
UPC	78285636968
UNSPSC	40141725

Clamp is fitted for copper tube and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

