

CADDY® SWIFT CLIP Strut Clamp for Insulated Tube/Pipe

TSMI0100



Features

- Secures pipe and insulation without a break, providing an uninterrupted vapor barrier seal which eliminates sweating on metal fittings
- Snap-in and twist installation requires no tools
- Fits directly into vertical and horizontal strut channels
- For support and positioning of refrigeration, A/C tubing, PEX piping, conduit and cabling
- Compliant with UL® 2043 and suitable for use in air handling spaces

Product Specifications

Part Number	TSMI0100
Material	Polyamide
Temperature	-40 to 284 °F
Outer Diameter (OD)	1"
Pipe Size	3/4"
Width (W)	1 5/8"
Standard Packaging Quantity	100 pc
UPC	78285659855
UNSPSC	40141725

Part Number	Copper Tube with 3/8" Insulation	Copper Tube with 1/2" Insulation
TSMI0062	-	-
TSMI0075	-	-
TSMI0087	-	-
TSMI0100	1/4"	-
TSMI0112	3/8"	-
TSMI0125	1/2"	1/4"
TSMI0137	5/8"	3/8"
TSMI0150	7/8"	5/8"
TSMI0162	1 1/8"	3/4"
TSMI0200	-	7/8"
TSMI0212	1 3/8"	1 1/8"

Can also be used with PEX piping. For PEX pipe sizes, refer to the Copper Tube Size column.

