

FEATURES

- Full distribution LED troffer
- Direct replacement for 1x4, 2x2 and 2x4 fluorescent
- Long-life, 60,000 hour LEDs at L80 reduce life cycle maintenance costs
- Multiple lens options
- Choice of two door frame options
- Four color choices with excellent color consistency and 82 CRI
- Fixed output, step dimming, or 0-10V dimming drivers available
- Hinged optical system allows easy access to LED modules and electrical from below the ceiling
- Metal to metal light leak protection on all sides of shielding frame
- All models standard with IC rating
- Recessed, surface, or cable mount
- Low W/ft² ratio typically meets the most restrictive lighting power density codes
- DesignLights Consortium® (DLC) qualified; see www.designlights.org
- Available with exclusive wiHUBB technology preinstalled
- QR code traceability
- Five year warranty (Terms and Conditions apply)



ORDERING INFORMATION


LJT								U			
MODEL	COLOR TEMP	CEILING TYPE	SHIELDING	DRIVER	VOLTAGE	OPTIONS					
LJT LED Lensed Troffer	30 3000K 35 3500K 40 4000K 50 5000K	G Grid ¹ SM Surface Mount CM Cable Mount ²	A12 Pattern 12 Acrylic Lens A12125 Pattern 12 Acrylic Lens, 0.125" Nominal A12F Pattern 12 Frosted Acrylic Lens A12125F Pattern 12 Frosted Acrylic Lens, 0.125" Nominal A19 Pattern 19 Acrylic Lens, 0.156" Nominal A19F Pattern 19 Frosted Acrylic Lens .156"	E Fixed Output ESD Step Dimming ED 0-10V Dimming	U 120V-277V	C388 3-Wire Flex C488 4-Wire Flex C588 5-Wire Flex ELL14 Emergency Battery Pack Installed, 1400 Lumen ^{3,4} GLR Fast Blow Fuse G1 Single Gasketing (Door to Housing) G2 Double Gasketing (G1 and Lens to Door) G3 Triple Gasketing (G2 and Housing to Ceiling) WIH wiHUBB ^{5,6} EOR End of Row (SM/CM only) ⁷ INT Intermediate (SM/CM only) ⁷ GTD Generator Transfer Device					
SIZE	LUMEN OUTPUT	DOOR									
14 1' x 4'	LW Low Watt ML Medium Lumen HL High Lumen VL Very High Lumen XL Extra High Lumen (2x4 only)	FS White Flush Steel FA White Flush Aluminum	For more door options contact factory.								
See Product Availability table below.											
<h4>ACCESSORIES (ORDER SEPARATELY)</h4> <p>FK14 1' x 4' Single Flange Kit FK22 2' x 2' Single Flange Kit FK24 2' x 4' Single Flange Kit FKCR Flange Kit Row Adaptor (All Sizes) CM48Y2SC3F-KIT 48" Cable Mount Kit for 2' Wide CM Ceiling Type, 3 Wire Feed Cord CM48Y1SC3F-KIT 48" Cable Mount Kit for 1' wide Cable Mount Fixtures, 3-Wire</p>											

¹ For drywall, order G with Flange Kit Accessory.
² Order hanger accessories separately.
³ For compatibility with Dual-Lite LiteGear® inverters in lieu of EL Battery Pack, contact Hubbell Lighting Representative.
⁴ Not available with 2x2 Surface or Cable Mount.
⁵ Not available with Surface Mount ceiling types.
⁶ In-Fixture Module Antenna adds 2" to overall fixture height at power feed location.
⁷ Provides ends with wiring access for continuous row mounting.
 Damp Label - standard. IC Rating - standard.


PRODUCT AVAILABILITY

SIZE	LUMEN PACKAGE	LUMENS	WATTS	LPW
14	LW	2485-2605	26	97-102
	ML	3605-3860	39	92-98
	HL	4430-4755	51	88 - 94
	VL	4920-5350	55	91 - 97
22	ML	3,200 - 3,450	35	92-99
	HL	3,775 - 4,025	43	89-94
	VL	4,250 - 4,550	51	85-91
24	LW	4,050 - 4,325	39	107-112
	ML	4,600 - 4,900	45	103-109
	HL	5,350 - 5,650	49	110-115
	VL	6,825 - 7,200	68	102-107
	XL	8,250 - 8,775	85	98-104


Based on A12 lens, range represents 3000K through 5000K.
 Lumens vary according to color temperatures and other factors. See specific photometric test(s).




LJT24




LJT24 SM or CM




LJT22



LJT22 SM or CM



LJT14



LJT14 SM or CM