

WASKO™ EYEWEAR

AVAILABLE IN SCRATCH-RESISTANT & ANTIFOG LENS COATINGS



BECAUSE YOU TAKE **SAFETY** PERSONALLY™

KEY PRODUCT ATTRIBUTES

- Economical
- Meets ANSI Z87.1-2010
- Provides 99.9% UV protection
- One-piece molded, polycarbonate frame and lens
- Bayonet-style, polycarbonate frosted temples with black rubber sleeves
- Polycarbonate nosepiece integrated into the lens
- Wraparound lens construction with two focal points
- Hinge to hinge: 5.45" L
- Lens width: 1.76" W

Padded flexible temples



5JE27



1FYX9



1FYY1



1FYY2



4VCH1



4VCH2



4VCH3



4VCH4



4VCH5

Model Number	Lens Color	Lens Coating	Frame Color	Visible Light Transmission (VLT) Range (%)
5JE26	Clear	Scratch Resistant	Frosted Clear	Over 90%
5JE27	Gray	Scratch Resistant	Frosted Gray	13 ± 3%
1FYX9	Amber	Antifog, Scratch Resistant	Frosted Amber	88 ± 3%
1FYY1	Indoor/Outdoor	Scratch Resistant	Black/Clear	50 ± 5%
1FYY2	Light Blue	Antifog, Scratch Resistant	Frosted Blue	71 ± 3%
4VCH1	Clear	Antifog	Clear	Over 90%
4VCH2	Gray	Antifog	Gray	13 ± 3%
4VCH3	Silver Mirror	Scratch Resistant	Gray	15 ± 5%
4VCH4	Rainbow Mirror	Scratch Resistant	Gray	13 ± 5%
4VCH5	Red Mirror	Scratch Resistant	Gray	30 ± 5%

©2015 W.W. Grainger, Inc. W-WEXC902 8SP6674