

DOOR LOUVERS

HVAC/R fact sheet

EXTRUDED ALUMINUM AND PAINTED STEEL DOOR LOUVERS

Both the Extruded Aluminum and Painted Steel models are heavy duty door louvers. The flanged frame has welded and/or staked mitered corners for added strength. The blades are inverted V style spaced on approximately 5/8" centers for maximum privacy. The louvers can be used for the transfer of air through any barrier and are ideal for use with 1-3/8" to 2-1/4" thick wood or metal doors. Available in Extruded Aluminum or Painted Steel and comes standard with color matched #8 x 3/4" Phillips head mounting screws. The Aluminum Design comes standard with a 204-R1 Clear Anodized Finish. The Steel Design comes standard with a Gray Primer Finish.



5NKL2



6WRK3

AVAILABLE SIZES:

SIZE	HOLE OPENING		ACTUAL OD		ALUMINUM ITEM NO.	STEEL ITEM NO.
	W	H	W	H		
8 X 8	8 1/2"	8 1/2"	10 1/4"	10 1/8"	6WRK4	6WRH6
10 X 4	10 1/2	4 1/2	12 1/4	6 1/8	6WRK5	6WRH7
12 X 8	12 1/2	8 1/2	14 1/4	10 1/8	6WRK6	6WRH8
12 X 12	12 1/2	12 1/2	14 1/4	14 1/8	5NKK9	6WRH9
14 X 8	14 1/2	8 1/2	16 1/4	10 1/8	5NKL0	6WRJ0
14 X 12	14 1/2	12 1/2	16 1/4	14 1/8	5NKL1	6WRJ1
16 X 8	16 1/2	8 1/2	18 1/4	10 1/8	5NKL2	6WRJ2
16 X 16	16 1/2	16 1/2	18 1/4	18 1/8	5NKL3	6WRJ3
18 X 12	18 1/2	12 1/2	20 1/4	14 1/8	5NKL4	6WRJ4
20 X 10	20 1/2	10 1/2	22 1/4	12 1/8	5NKL5	6WRJ5
20 X 12	20 1/2	12 1/2	22 1/4	14 1/8	5NKL6	6WRJ6
20 X 14	20 1/2	14 1/2	22 1/4	16 1/8	5NKL7	6WRJ7
20 X 16	20 1/2	16 1/2	22 1/4	18 1/8	5NKL8	6WRJ8
20 X 20	20 1/2	20 1/2	22 1/4	22 1/8	5NKL9	6WRJ9
24 X 12	24 1/2	12 1/2	26 1/4	14 1/8	5NKN0	6WRK0
24 X 16	24 1/2	16 1/2	26 1/4	18 1/8	5NKN1	6WRK1
24 X 18	24 1/2	18 1/2	26 1/4	20 1/8	5NKN2	6WRK2
24 X 24	24 1/2	24 1/2	26 1/4	26 1/8	5NKN3	6WRK3

Find it at Grainger.

Call or visit your local branch or go to grainger.com/dayton
for complete product line information.