

PORTABLE GENERATORS GASOLINE OR DIESEL-FIRED Fact Sheet



PERFECT FOR:

Providing power for most industrial and contractor needs.

FEATURES:

- Honda OHV gasoline engines or Kohler Diesel engines
- Electric start (6500-12000 watt models), dry battery included
- Brushless alternators with 100% copper windings
- Heavy-duty, powder coated, wraparound frame with 1-inch steel tubing
- Wheel kit (4400-12000 watt models)
- Easy-access and protected control panels with magnetic circuit breakers and GFCI-protected receptacles
- Large, low-tone mufflers
- USDA/USFS-approved spark arrestors
- Fuel shut-off valves (5000-6500 watt models)
- Easy to read fuel gauges (5000-12000 watt models)
- Voltmeters/hour meters (5000-12000 watt models)



2ZRP6



2ZRP9



6FYA4

UNIT DIMENSIONS
(IN.)

SKU NO.	RATED AC OUTPUT	ENGINE	ALTERNATOR	RECEPTACLES	CIRCUIT BREAKERS	UNIT DIMENSIONS (IN.)			NET WT. (LB.)
						L	W	H	
2ZRP6	2450 watts	163cc Honda OHV Gasoline	120V, 60Hz	(1) 120V, 20A GFCI duplex	(1) 20A push-button	25	18	18	130
38AW97	4400 watts	270cc Honda OHV Gasoline	120V/240V, 60 Hz	(2) 120V, 20A GFCI duplex; (1) 120V/240V, 20A twist lock; (1) 120V, 30A twist lock	(2) 20A toggle, single pole; (1) 20A toggle, double pole; (1) 30A toggle, single pole	29	19.75	22.5	176
2ZRP8	5000 watts	389cc Honda OHV Gasoline	120V/240V, 60 Hz	(2) 120V, 20A GFCI duplex; (1) 120V/240V, 20A twist lock; (1) 120V, 30A twist lock	(1) Main circuit breaker; (2) 20A toggle, single pole; (1) 20A toggle, double pole; (1) 30A toggle, single pole	29	24.4	22.5	210
2ZRP9	6500 watts	389cc Honda OHV, Gasoline, electric start	120V/240V, 60 Hz	(2) 120V, 20A GFCI duplex; (1) 120V, 30A twist lock; (1) 120V/240V, 30A twist lock	(2) 20A toggle, single pole; (1) 30A toggle, single pole; (1) 30A toggle, double pole	29	24.4	22.5	233
6FYA4	12000 watts	688cc Honda OHV, Gasoline, electric start	120V/240V, 60 Hz	(2) 120V, 20A GFCI duplex; (1) 120V, 30A twist lock, (1) 120V/240V, 30A twist lock; (1) 120V/240V, 50A	(2) 20A toggle, single pole; (1) 30A toggle, single pole; (1) 30A toggle, double pole; (1) 50A toggle, double pole	31.5	30.5	37.5	508
36C206	5000 watts	9.1 HP Kohler Diesel, electric start	120V/240V, 60 Hz	(2) 120V, 20A GFCI duplex; (1) 120V/240V, 20A twist lock; (1) 120V, 30A twist lock	(1) main circuit breaker; (2) 20A toggle, single pole; (1) 20A toggle, double pole; (1) 30A toggle, single pole	29	21.62	22.5	273

Call or visit your local branch or go to Grainger.com/Dayton for complete product line information.