

# Move Up to the Superior Solution for Dynamic Tire Balancing

Dyna Beads® are ultra smooth, high density ceramic spheres that travel inside the tire to locate themselves opposite heavy points to eliminate out-of-balance motion.



Dyna Beads® dynamically balance tires on the move, providing a smoother ride that lasts the life of the tire. Dyna Beads® will not deteriorate, break up, or grind down like glass or steel media. They don't slide around inside your tire -- they roll, protecting your inner liner and preventing premature air loss.



Dyna Beads® are more effective than mechanical balancers, for a fraction of the cost. The balance weight is at the outermost point of the tire for greater efficiency ounce for ounce. You'll also maintain full brake cooling without the mass of a balancer restricting airflow.

Dyna Beads® 100% ceramic composition works better for trucks because they are impervious to moisture. They won't "clump" like powders or granules. This is extremely important for long-haulers, especially those traveling north in winter, when condensation is likely.

Dyna Beads® were designed to provide a reliable balancing solution for commercial trucks that will perform for the long haul, better than any other internal media.



- Better tire mileage & longer life
- Won't clump with moisture, for year-round performance
- Smooth ride for the life of the tire
- Will not grind down or abrade inner liner
- Fast, clean application -- no messy powders
- No special valve cores or tools
- PBS, TPMS & Nitrogen compatible

Give your fleet the superior tire balancing solution and drive more profit to your bottom line

CALL TOLL-FREE: 1.866.352.7251 or visit [www.dynabeads.com/fleets.htm](http://www.dynabeads.com/fleets.htm)