

SPILLPAL™

THE MOST AFFORDABLE, AND CONVENIENT TEMPORARY STORAGE.

The flexible-sidewall SpillPal™ line is the easiest to use and the most affordable hazardous material storage product on the market today. SpillPal™ provides incidental spill control during temporary storage of drums, machine parts, tanks, and generators. It can also be used as a washdown pad or pumping station. A great alternative to hard plastic pallets, the ENPAC® SpillPal™ features foam sidewalls that easily spring back into place after any type of pressure is applied. With 6 configurations and custom sizes available, SpillPal™ is perfect for any job.



SEE PG 70
FOR CHEMICAL
COMPATIBILITY
GUIDE



Reusable! When you're done, just clean, fold, and place on a shelf!
Frees up valuable floor space!



SPILLPAL™

| Part # | Description | Dimensions L x W x H ft. (m) | Weight lb. (kg) | Spill Cap. gal. (L) |
|----------------------|---------------------------------|-------------------------------|-----------------|---------------------|
| 5750-YE 5750-YE-G | 1-Drum (with grate) | 2 x 2 x 3" (.6 x .6 x 8 cm) | 2 (1) | 10 (38) |
| 5755-YE 5755-YE-G | 2-Drum (with grate) | 2 x 4 x 3" (.6 x 1.2 x 8 cm) | 4 (2) | 15 (57) |
| 5760-YE 5760-YE-G | 4-Drum (with grates) | 4 x 4 x 3" (1.2 x 1.2 x 8 cm) | 5 (2.5) | 30 (114) |
| 5765-YE 5765-YE-G | 4-Drum In-Line (with grates) | 2 x 8 x 3" (.61 x 2.4 x 8 cm) | 6 (2.7) | 30 (114) |
| 5770-YE 5770-YE-G | 6-Drum (with grates) | 4 x 6 x 3" (1.2 x 1.8 x 8 cm) | 7 (3.2) | 45 (170) |
| 5775-YE 5775-YE-G | 8-Drum (with grates) | 4 x 8 x 3" (1.2 x 2.4 x 8 cm) | 9 (4.1) | 60 (227) |

Regulations: EPA 40 CFR 264.175, SPCC and NPDES

Store anything from one drum to two IBCs! Six models are available, each with optional grates.



No need for ramps. Flexible sidewalls spring back to form. Allows easy drive-in and drive-out with a hand truck or forklift. The 4-drum unit holds one IBC; 8-drum unit holds two (2) IBCs.

GRATES

New replacement grates are available for when contamination occurs. Call ENPAC® customer service for details.

GRATES

| Part # | Description | Dimensions L x W x H in. (cm) | Weight lb. (kg) |
|---------|-------------|-------------------------------|-----------------|
| 7006-BK | Full Grate | 48 x 23 x 2 (122 x 58 x 5) | 18 (8) |
| 7007-BK | 1/2 Grate | 24 x 23 x 2 (61 x 58 x 5) | 9 (4) |

