



PROWLER POOL™

THE EASIEST, LIGHTEST SPILL CONTAINMENT POOL AVAILABLE.

Prowler Pop-up Pools™ offer excellent resistance to the widest range of chemicals, acids, fuels, and other hazardous materials. They are also resistant to abrasions, punctures, UV Rays, and cold temperatures as low as -60° F. The Prowler is half the weight of comparably sized pools while offering twice the strength. Fits easily into spill response kits.



Lightweight, compact and portability makes the Prowler Pool™ excellent for immediate spill response.



PROWLER POOL™

Part #	Description	Base dia. in. (cm)	Top dia. in. (cm)	Height in. (cm)	Weight lb. (kg)	Spill Cap. gal. (L)
5920-YE	20-Gallon	28 (71)	18 (46)	13 (36)	2 (1)	20 (75.7)
5966-YE	66-Gallon	48 (122)	36 (91)	14 (33)	3 (1.4)	66 (250)
5900-YE	100-Gallon	48 (122)	32 (81)	18 (46)	5 (2.3)	100 (378.5)
5950-YE	150-Gallon	60 (152)	44 (112)	18 (46)	8 (3)	150 (567.8)

Regulations: EPA, SPCC and NPDES



HAZMAT POOL™

The Hazmat Pool™ is an inexpensive, quick deployment pool that is small enough to be stored on any truck or emergency response vehicle. Decontaminate for reuse or discard according to regulations.

Hazmat Pool™ has excellent puncture abrasion and chemical resistance along with a -60° F cold crack. With resistance to the widest range of chemicals, and just seconds to set up, the ENPAC® Hazmat Pool™ is your answer to decontamination. Optional drain.

HAZMAT POOL™

Part #	Description	Base in. (cm)	Top in. (cm)	Height in. (cm)	Weight lb. (kg)	Spill Cap. gal. (L)
5901-YE	100-Gallon	74 (188)	67 (170)	8 (20)	5 (2.3)	100 (378.5)
5901-YE-D	w/drain					

Regulations: EPA 40 CFR 264.175, SPCC and NPDES



SEE PG 70 FOR CHEMICAL COMPATIBILITY GUIDE