



**SPECIFICATIONS - ERG50**

1. INSTALLS 18-50 LB (80-222 N) CABLE TIES
2. ADJUSTABLE TENSION SETTINGS 1-8
3. INTEGRATED TENSION LOCKING SCREW
4. 360° ROTATING NOSE
5. ANTI-RECOIL MECHANISM
6. ADJUSTABLE GRIP SPAN
7. SELECTABLE MODE HIGH-LOW HANDLE FORCE
8. 1" [25.4mm] STROKE IN HIGH, 0.5" [12.7mm] STROKE IN LOW
9. HIGH IMPACT POLYMER CONSTRUCTION WITH SOFT OVERMOLDED GRIP
10. SPARE BLADE STORAGE - SPARE BLADE PART# - CDS010461

<b>GENERAL NOTES</b>		THIRD ANGLE PROJECTION		 www.tnb.com			
1. ALL DIMENSIONS ARE FOR REFERENCE ONLY. 2. DIMENSIONS IN BRACKETS [ ] ARE IN METRIC UNITS.							
<b>REVISIONS</b>		ORIGINAL PROJECT NO / ( ERN NO )		SHEET NO:	REV. NO:	DRAWING NO:	
- SEE ERN ( **** ) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****		FD55446 / ( 2008035 )		1 OF 1	-	WSD000333	