

<b>Name</b>	Socket Weld Flange
<b>Product Code</b>	S1014SW4020N
<b>Product Name</b>	2" 304/L Stainless Steel Forged 150# ANSI RF Socket Weld Flange
<b>Family Code</b>	S1014SW4
<b>Alloy</b>	304\304L Stainless Steel
<b>Bore Schedule</b>	Sch 40
<b>Pressure Rating</b>	150#
<b>Size</b>	2"
<b>Outside Diameter</b>	6.00"
<b>Thickness</b>	0.75"
<b>Raised Face Diameter</b>	3.62"
<b>Bore</b>	2.44"
<b>Length Through Hub</b>	1.00"
<b>Depth of Socket</b>	0.62"
<b>Hub Diameter</b>	2.56"
<b>Bolt Circle</b>	3.88"
<b>Bolt Hole Size</b>	0.62"
<b>Holes Diameter</b>	0.62"
<b>Number Of Bolt Holes</b>	4
<b>Materials</b>	Forged Stainless Steel
<b>Weight</b>	5.0706
<b>Standards</b>	ASME A182 (Forging), ASME B16.5 (Dimensions), ASME B1.20.1 (Threads)

