



GREENLEE®
A Textron Company

**MADE
FOR THE
TRADE**

HIGH LEVERAGE SIDE-CUTTING PLIERS

AVAILABLE SIZES:
8", 9"

Exceeds ASME/ANSI
Specifications



HIGH LEVERAGE SIDE-CUTTING PLIERS

FEATURES	BENEFITS
1 Tapered/Flared Handles	Allows for increased leverage when cutting large diameter wire.
2 Ergonomic Flattened Oval Grip Profile	Allows for a larger load surface to increase comfort and reduce user fatigue.
3 Extended Grip	Creates extra control and comfort when "choked up" on the tool for small, repetitive jobs.
4 Induction-Hardened Cutting Knives	For superior cutting capability, wear resistance and long life.
5 Precision-Machined Cross Hatch Jaws	For maximum gripping.
6 New England Style Head	Standard to North American industry.
7 Brushed Finish	For professional look and longer wear.
8 Riveted Joint	For precision feel, smooth action with minimum joint looseness.
9 Specially Designed Handle	Size and shape of metal handle designed to reduce shock while cutting wire.
10 Integral Thumb Stops	To reduce slipping and allow user maximum tool control.
11 Identification Area	To allow user to personally label or identify their tool.

Note: This is not an insulated tool.

High Leverage Side-Cutting Pliers

CAT. NO.	UPC NO.	DESCRIPTION
0151-08M	54701	High Leverage Side-Cutting Pliers 8" Molded Grip
0151-09M	54702	High Leverage Side-Cutting Pliers 9" Molded Grip
0151-09M-CP	95925	High Leverage Side-Cutting Pliers 9" Counter Pack (Qty 5)

SPECIFICATIONS	8"	9"
Overall Length	8-1/2" (21.6 cm)	9-3/8" (23.8 cm)
Weight	.87 lbs. (.04 kg)	1.13 lbs. (.51 kg)

International Tel: +1.815.397.7070
Fax: +1.815.397.9247

Canada Tel: 800.435.0786
Fax: 800.524.2853

USA Tel: 800.435.0786
Fax: 800.451.2632



4455 BOEING DRIVE, ROCKFORD, IL 61109-2988 USA
GENERAL OFFICES: 815.397.7070

www.greenlee.com

MA-4900 11/06 ©2006 Greenlee Textron Inc.
Greenlee Textron Inc. is a subsidiary of Textron Inc.