

# MICRO SWITCH™ BZE6/BZV6 Enclosed Basic Switch Product Nomenclature



For example, a **BZE6-2RN** part number would define a BZE6 side-mount die-cast zinc enclosed basic switch with 15 A circuitry, SPDT with a standard contact and boot seal.



Switch Type	Enclosure Type	Contact Gap	Contact	Plunger Type	Actuator Modifications	Additional Modifications
<b>BZ</b> BZ Series Enclosed Basic Switch SPDT, 15 A	<b>E6</b> Side mount, die-cast zinc <b>V6</b> Flange mount version of E6	<b>2</b> 0.020 in <b>7</b> 0.070 in	<b>R</b> Standard	<b>N</b> Seal boot <b>Q</b> No seal boot	Pin plunger <b>X</b> Maintained contact with reset plunger <b>2</b> Adjustable roller lever <b>4</b> Manual, palm button <b>7</b> #8 mounting screws <b>8</b> <b>80</b> Roller plunger <b>18</b> Coil spring wobble stick <b>28</b> One-way roller lever <b>34</b> Low temp. <b>62</b> Rod lever <b>72</b> <b>722</b> Gold-contact basic <b>81</b> Cross roller plunger	<b>C3</b> Pre-leaded, 3 ft cable, conduit area only potted <b>F3</b> Fully potted, 3 ft of cable <b>F5</b> Fully potted, 5 ft of cable <b>F6</b> Fully potted, 6 ft of cable <b>FR</b> Fully potted, 4-pin "mini style" connector <b>R</b> 4-pin "mini style" connector <b>S</b> 1/4-14 NPSM conduit threads <sup>2</sup> <b>5</b> Pre-leaded, 5 ft cable, conduit area potted

NOTE: not all combinations of model code are available.  
Please contact your Honeywell provider/representative for assistance.

<sup>1</sup> "X" requires "blank" for actuator connector cap

<sup>2</sup> No connector or cable option available