

# MICRO SWITCH™ GLL Global Limit Switch Product Nomenclature

**Honeywell**

For example, a **GLLA01C** part number would define a GLL Series global limit switch with 1/2-14 NPT conduit, 1NO/1NC snap action contact, and a top roller plunger.



GLL	A	01	C	
Switch Type	Conduit	Contact Block	Head/Actuator	Lever Style
<b>GLL Series Global Limit Switch</b>	<b>A</b> 1/2-14 NPT	<b>01</b> 1NO/1NC snap action	<b>A</b> Side rotary (requires lever)	<b>1B</b> Fixed plastic (25 mm R) 17 mm metal roller
	<b>C</b> 20 mm	<b>03</b> 1NO/1NC snap action, BBM	<b>B</b> Top pin plunger	<b>1Y</b> Fixed plastic, 50mm rubber roller
		<b>04</b> 1NO/1NC slow action, MBB	<b>C</b> Top roller plunger	<b>2B</b> Adjustable metal, (R20-R75) 17 mm metal roller
		<b>06</b> 2NC slow action	<b>D</b> Top horizontal roller plunger	<b>2Y</b> Adjustable metal, 50mm rubber roller
			<b>F</b> Top vertical roller plunger	<b>3B</b> Fixed plastic (31.55 mm R) 17 mm metal roller
				<b>4J</b> Ø3 mm adjustable metal rod, (22 mm - 150 mm)

NOTE: not all combinations of model code are available.  
Please contact your Honeywell provider/representative for assistance.