



134 Marbledale Road, Tuckahoe, NY 10707 phone 914-793-0700 fax 914-793-4527
OK Industries sales@jonard.com www.jonard.com
Div. of Jonard Industries www.okindustries.com

SPECIFICATION

Part Numbers: R24Color-0100/1000 ROLLS
For Cut/Strip/Wrap Applications

This specification is for wire per UL Style 1422, 105°C, no voltage rated, 24 AWG. Solid silver plated oxygen free copper.

CONDUCTOR:

Size: 24 AWG. Solid
Circular Mil Area: 394 Minimum
Material: Silver plated oxygen free, high Conductivity copper per ASTM-B 170
DC Resistance: @20°C(68°F) max. 26.2 Ω/M'

Elongation: 20% before insulation
Plating: Silver, 40 micro-inch minimum per ASTM-B 298.
Weight: 1.22 lbs/M'
Diameter: 0.0201" nom.
0.0200"min.

INSULATION:

Material: Kynar 460
Diameter: 0.0316" ± .0015"
Min. Avg. Wall: 0.005"
Min. any. Pt.: 0.004"
Spark Test: 2,000VAC RMS
Color: As specified
Weight: 0.333 lbs/M'
Total Weight: 1.55 lbs/M'
Flammability: VW-1

M' = 1000 Feet