



MAKE YOUR MARK

MEASURING WHEELS

KESONITE™ WHEELS

Kesonite is a strong, dense metal/resin composite that holds its shape better than metal and is stronger than a spoked or die cast wheel. The weight of the wheel makes it easier to use and more accurate on rough terrain. The design is based on our popular RR large series but includes a new wheel design, material, and safety reflector.



EASY-READ, MAGNIFIED COUNTER

5-digit, easy-to-read, magnified counter measures 9,999 feet, 11 inches (9,999.9 ft. on engineers' model and 9,999.9 meters on metric).

NOW WITH A 3-PC. PISTOL GRIP HANDLE!

The same outstanding features, benefits and reliability of our previous 2-piece handle version with the added convenience of our **new 3-piece, pistol grip handle**. **The twist locks have been replaced with quick-snap cam locks**. The new handle telescopes down to a **more compact 23 inches** for ease of transport and more compact storage.



Limited lifetime warranty.

MODEL	UPC (052837)	UNITS	DIA.	CIRC.	SPECIAL FEATURES
RR30	026425	ft., in.	11-1/2 in.	3 ft.	Increased strength & weight
RR3010	026524	ft., 10ths	11-1/2 in.	3 ft.	Increased strength & weight
RR30M	026500	m, dm	.318 m	1 m	Increased strength & weight
RR40	026463	ft., in.	15-1/2 in.	4 ft.	Increased strength & weight



RR30

Kesonite Series Wheel Sell Sheet