



MAKE YOUR MARK

MEASURING WHEELS

MP SERIES METAL PROFESSIONAL SOLID WHEELS

A sliding tool box or a shovel in the back of a truck has destroyed the precision of many spoked wheels. Keson solid plastic wheels are made to withstand abuse and are not nearly as susceptible to these impacts. Unlike spoked wheels our solid wheels will not dent or bend, maintaining a perfect circumference. If your job takes you through fields or trails with twigs, sticks, tall grasses and other brush, consider a solid wheel option, which prevents debris from locking up the wheel.

FEATURES

- No spokes to catch grass or sticks.
- No spokes to bend or snap.
- Solid molded wheels do not dent or bend, maintaining a perfect circumference



EASY-TO-READ COUNTER

Our geared Mechanical Clicker Counter features easy-to-read numbers.

MP415

The counter measures feet and there are two scales molded into the hub of the wheel itself: inches on one side and 10ths on the other.

MP315M

On our metric version, decimeter graduations are molded into the hub of the wheel.

MP201

Strong, rigid, 1-piece steel handle — strongest in the industry. Without a collapsing point in the handle, there is no weak point on this frame. This solid wheel is two inches wide, giving it better traction on sand, loose gravel and wet ground; a favorite among landscapers.



Limited lifetime warranty.

MODEL	UPC (052837)	UNITS	DIA.	CIRC.	SPECIAL FEATURES
MP201	008315	ft.	7-1/2 in.	2 ft.	Solid molded wheel
MP315M	027040	m, dm	.318 m	1 m	Solid, metric
MP415	026449	ft., in & ft., 10ths	15-1/2 in.	4 ft.	Solid, two scales wheel



MP415

MP201