



MAKE YOUR MARK

LONG TAPE MEASURES

NRS SERIES

Features metal, planetary gearing for super-fast rewind and no more stripping gears and high-visibility orange polycarbonate case. Tough, double nylon-coated steel blade assures long life under field use. Rubber-grip shovel handle provides comfortable, rapid reeling. Wide base crank with metal reinforcement for increased durability.



NRS18200

Limited lifetime warranty.

MODEL	UPC (052837)	LENGTH	UNITS	ZERO PT.	ATTACHMENT	BLADE
NRS18100	020980	100 ft.	ft, in, 1/8	Hook End	Hook	E1
NRS10100H	022687	100 ft.	ft, 1/10, 1/10	Hook End	Hook	E22
NRS18M100	028061	100 ft./30m	ft, in, 1/8 & m, cm, mm	Hook End	Double Hook	E1 & E15
NRS18200	021000	200 ft.	ft, in, 1/8	Hook End	Hook	E1
NRS10200H	022694	200 ft.	ft, 1/10, 1/10	Hook End	Hook	E22
NRS18M200	028078	200 ft.	ft, in, 1/8 & m, cm, mm	Hook End	Double Hook	E1 & E15
NRS18300	021017	300 ft.	ft, in, 1/8	Hook End	Hook	E1
NRS10300H	022670	300 ft.	ft, 1/10, 1/10	Hook End	Hook	E22
NRS30M	027484	30m	m, cm, mm	Tape End + .3m	Hook	E17
NRS50M	027491	50m	m, cm, mm	Tape End + .3m	Hook	E17
NRS100M	027507	100m	m, cm, mm	Tape End + .3m	Hook	E17

AVAILABLE IN

E = 3/8-inch wide, 2x nylon coated steel, long tape



E1 = Hook, Zero = Hook end, SAE: ft., in., 1/8



E15 = Double Hook, SAE (Black and Red)/Metric (Red): ft., in., 1/8 & cm, mm



E17 = Ring, Zero = Tape end + .3 meters, Metric: cm, mm



E22 = Hook, Zero = Hook end, ENG: ft., 1/10, 1/100

NRS Series Long Tape Sell Sheet