



MAKE YOUR MARK

SHORT TAPE MEASURES

AUTOMATIC LOCK

Our fastest growing specialty tape series. These tapes feature blades that when pulled out, stay out, without the user needing to engage a lock. The push button release frees the blade from its locked state, allowing it to travel back into the case. These tapes come with a rubber-grip compact housing. Available in both chrome and high visibility orange.



HV PG1825ALV

PG1825AL

HV = High Visibility Option

FEATURE	DEFINED	RATING
Lock	Automatic, button-release	● ● ● ● ○
Case & Components	Chrome-Coated ABS	● ● ● ● ○
Blade	Nylon-Coated Steel	● ● ● ● ○
Impact Durability		● ● ● ● ○
Overall: 4.00		

Limited warranty.

MODEL	UPC (052837)	LENGTH	UNITS	WIDTH (in.)	STAND OUT (ft.)	BLADE (page 30)
PG1825AL	027606	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B1
PG181025AL	027705	25 ft.	ft, 1/10, 1/100 & ft, in, 1/8, 1/16	1	up to 8	B4
PG18M25AL	027866	7.5 m/25 ft.	ft, in, 1/8, 1/16 & cm, mm	1	up to 8	B5
PG10M25AL	027712	7.5 m/25 ft.	ft, 1/10, 1/100 & cm, mm	1	up to 8	B6
PG1825ALV	027804	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B1
PG1825ALVMAG	027811	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B9

AVAILABLE IN

B = 1-inch wide, 2x nylon-coated, short tape



B1 = SAE: ft., in., 1/8, 1/16 (1/32 in. first ft.)



B4 = ENG/SAE: ft., 1/10, 1/100 & ft., in., 1/8, 1/16



B5 = SAE/M: ft., in., 1/8, 1/16 & cm, mm



B6 = ENG/M: ft., 1/10, 1/100 & cm, mm



B9 = Magnet, SAE: ft., in., 1/8, 1/16 (1/32 in. first ft.)

Automatic Lock Series Short Tape Sell Sheet