



MAKE YOUR MARK

SHORT TAPE MEASURES



PROFESSIONAL

The stainless steel housing offers our highest impact resistance and all Pro series feature a slotted rubber grip. The tape lock is stronger than our other offerings as well. The housing is larger than our Chrome and Autolock Series, but these tapes still easily fit into a tape holder. Available in both chrome and high visibility orange.



HV PGPRO1825V

HV = High Visibility Option

FEATURE	DEFINED	RATING
Lock	Slide	●●●●○
Case & Components*	Chrome-Coated ABS	●●●●●
Blade	Nylon-Coated Steel	●●●●○
Impact Durability		●●●●●
Overall: 4.50 *The High Visibility models are 4.0 overall, case durability is not as great as the stainless steel models.		

Limited warranty.

MODEL	UPC (052837)	LENGTH	UNITS	WIDTH (in.)	STAND OUT (ft.)	BLADE (page 30)
PGPRO1825	027545	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B1
PGPRO1830	027552	30 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B1
PGPRO1812V	027873	12 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	5/8	up to 4	A1
PGPRO1816V	027880	16 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B1
PGPRO1825V	027897	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B1
PGPRO1835V	027903	35 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1	up to 8	B1

AVAILABLE IN

A = 5/8-inch wide, 2x nylon-coated, short tape



A1 = SAE: ft., in., 1/8, 1/16 (1/32 first ft.)

B = 1-inch wide, 2x nylon-coated, short tape



B1 = SAE: ft., in., 1/8, 1/16 (1/32 in. first ft.)