



MAKE YOUR MARK

## SHORT TAPE MEASURES



### WIDE BLADE

Our wide blade tapes have 1 3/16-inch blades with bigger, bolder numbers. These blades also stand out up to 10 feet, making it easier for one person to get more measuring done. We have some users who prefer our brand to other wide blade tapes because they insist that when running it up a wall (with the attachment on the floor), our tape travels higher before falling away from the wall. Available in both chrome and high visibility orange.



**HV** PG1825WIDEV

**HV** = High Visibility Option

FEATURE	DEFINED	RATING
Lock	Slide	●●●●○
Case & Components	Chrome-Coated ABS	●●●●●
Blade	Nylon-Coated Steel	●●●●●
Impact Durability		●●●●○

Overall: **4.25**

Limited warranty.

MODEL	UPC (052837)	LENGTH	UNITS	WIDTH (in.)	STAND OUT (ft.)	BLADE (page 31)
PG1825WIDE	027538	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1-3/16	up to 10	C1
PG181025WIDEV	027781	25 ft.	ft, 1/10, 1/100 & ft, in, 1/8, 1/16	1-3/16	up to 10	C4
PG1825WIDEV	027835	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1-3/16	up to 10	C1

### AVAILABLE IN

**C = 1-3/16 inch wide, 2x nylon-coated, short tape**



C1 = SAE: ft., in., 1/8, 1/16 (1/32 in. first ft.)



C4 = ENG/SAE: ft., 1/10, 1/100 & ft., in., 1/8, 1/16

Wide Blade Series Short Tape Sell Sheet