



Head rotates 360°
Articulates 210°



Powerful magnet
attaches to steel surfaces
Includes a cover to protect
painted surfaces



Spring-loaded clip attaches
to turn-out gear and uneven
surfaces for convenient
hands-free lighting



Engineered optics feature dual parabolic reflectors within a larger textured reflector optimizing light on target in conjunction with an overall smooth flood pattern

Shockproof dual C4® premium LED technology delivers 200 lumens

Rubber dome push-button actuator is easy to operate even when wearing heavy gloves





High-impact, super-tough nylon polymer construction for exceptional durability

Dual power source: accepts rechargeable NiCd battery pack or 4 "AA" alkaline batteries



Alkaline battery pack holds 4 "AA" alkaline batteries

Designed to put light where you need it, the Knucklehead is the most versatile light you'll ever own.

FL 1 STANDARD	HIGH	LOW
	200 LUMENS	63 LUMENS
	3h 30min	16h
	68m	37m
	1150cd	350cd

4 modes: High, low, moonlight, flash
Moonlight mode runs 20 days
Flash runs 8 hours

Optimized electronics provide regulated intensity

2 meter impact-resistance tested

IPX4 rated for water-resistance

Removable magnet with 135 lb pull strength features a replaceable rubber boot

Serialized for positive identification

9.2 in. (23.4 cm); NiCd 23.1 oz (655 grams); Alkaline 18.3 oz (519 grams)

Available in orange

Limited lifetime warranty

Orange Knucklehead with Clip

Part #	Item Description
90657	Knucklehead - 120V AC/12V DC - Orange
90661	Knucklehead 120V AC Fast Charge - Orange
90670	Knucklehead 12V DC Fast Charge - Orange
90651	Knucklehead (without charger) Orange
90644	Knucklehead - Alkaline Orange - Blister

