



LOUISVILLE®

LADDERS TRUSTED BY THE PROS FOR OVER 65 YEARS

FS1400HD SERIES

375 lbs. TYPE IAA
load capacity*
*includes weight of user plus materials

FIBERGLASS STEP LADDER

FS1400HD FLYER 2013 v1 © 2013 Louisville Ladder, Inc. All rights reserved.



FS1406HD



SHOX™ - superior
impact absorption

ProTop™ - versatile
and durable

Da Boot™
Patent #7,000,731 B2

**Inside spreader
braces**

**Riveted step
construction
with gussets**

Wide back braces



MODEL	LADDER SIZE	STEP DEPTH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FS1403HD	3'	3"	17 13/16"	24 7/16"	11.7	2.4'
FS1404HD	4'	3"	19 9/16"	28 15/16"	15	3.7'
FS1405HD	5'	3"	21 1/16"	34 7/8"	17	4.8'
FS1406HD	6'	3"	22 9/16"	40 7/8"	21	6.1'
FS1407HD	7'	3"	24 1/16"	46 13/16"	25	7.5'
FS1408HD	8'	3"	25 9/16"	52 3/4"	28	8.7'
FS1410HD	10'	3"	28 9/16"	64 11/16"	34	12.6'
FS1412HD	12'	3"	31 9/16"	76 7/8"	51	16.7'



ANSI
Meets or exceeds requirements
of American National Standards Institute
ANSI A14.5



Visit us on facebook, YouTube, twitter

www.LouisvilleLadder.com | 1-800-666-2811