



# LOUISVILLE®

LADDERS TRUSTED BY THE PROS FOR OVER 65 YEARS

## FXP1700 SERIES

### FIBERGLASS PRO PLATFORM LADDER

**300** lbs. **TYPE IA** load capacity\*  
\*includes weight of user plus materials

EXTENDED HANDRAIL FOR ADDED COMFORT AND SAFETY

#### PRODUCTIVITY COMFORT & SAFETY

- Ergonomically positioned ProTop™ increases productivity
- Includes magnet and multiple tool slots
- 30% larger platform area for added comfort

ProTop™ versatile & durable



SHOX™ - superior impact absorption



Da Boot™ Patent #7,000,731 B2



Double-rivet step construction



Wide back braces



MODEL	HT. TO PLATFORM	STEP DEPTH	BOTTOM WIDTH	APPROX. SPREAD	APPROX. WT. (LBS)	APPROX. CUBES
FXP1702	2'	3"	21 1/4"	32 5/8"	18	6.4'
FXP1703	3'	3"	23 1/2"	38 5/8"	22	7.9'
FXP1704	4'	3"	24 1/2"	44 1/2"	24	9.6'
FXP1705	5'	3"	26 1/2"	50 1/2"	27	11.4'
FXP1706	6'	3"	27 3/4"	56 1/2"	30	13.4'
FXP1708	8'	3"	30 7/8"	68 1/4"	46	17.5'
FXP1710	10'	3"	33 4/5"	80 1/8"	60	21.8'
FXP1712	12'	3"	36 4/5"	92"	72	25.4'



FXP1706

FXP1700 FLYER 2014 v1 © 2014 Louisville Ladder, Inc. All rights reserved.



ANSI  
Meets or exceeds requirements  
of American National Standards Institute  
ANSI A14.5



Visit us on facebook, YouTube, twitter

[www.LouisvilleLadder.com](http://www.LouisvilleLadder.com) | 1-800-666-2811