



Position	Amount	Type number	Description	PG
1	1	316062290	Armature compl., 120V	
2	1	311012240	Feldpaket vollstaendig	28
3	1	344492750	Cable with UL-CSA-plug	23
4	1	344097360	Cable sleeve	11
5	1	343362490	Cable clip	12
6	1	141117060	Self-tap. fill. h. screw	12
7	2	344498880	Strand compl.	10
8	1	315013660	Motor housing	22
9	1	316053640	Shift lever compl.	17
10	1	343433780	Pivoting switch	10
11	1	143115170	Ball bearing,6x19x6	16
12	1	344097870	Rubber bushing	10
13	1	343430930	Baffle	16
14	1	143114880	Ball bearing, 8x22x7	19
15	1	343433770	Motor cap 2 part	19
16	3	141113180	Self-tap. fill. h. screw	10
17	4	141117060	Self-tap. fill. h. screw	12
19	1	315202620	Bearing flange	25
20	1	344161300	Open-end spanner	18
22	1	344099150	Handle	19
23	1	316051580	Spindle head with Spindle stop	35
24	1	343082850	Electronic unit,120V	31
25	1	343409640	Switch	19
26	2	316045980	Brush holder compl. cut out	21
27	1	316046900	Carbon brush set cut-off	22
28	1	399999990	Part not needed	
29	1	631949000	Collet 1/4"	
30	1	316062270	Carrier cpl.	
31	1	344099140	Buffer	13
35	1	338062530	Rating plate	10
36	1	338122090	Warning Label 52x22	11
61	1	341161360	Spindle shaft	32
62	1	143115270	Ball bearing,12x24x6	21
63	1	143111090	Ball bearing, 10x30x9	24
64	1	141180370	Retaining ring	10
65	1	143115490	Compensating washer	10
66	1	341071300	Coupling	18
70	1	143115470	Compensating washer	10
71	1	316051700	Luefter mit Staubschutzkorb	17
1001	1	338505710	Wiring diagram	

